


Passive Components > Resistors > Through-Hole Resistors

Resistor Type: **Power Resistor**Element Type: **Wire Wound, Ceramic Composition**Power Rating: **5 W**Resistance Class: **Up to 1k Ω** Resistance Value: **15 Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 $^{\circ}$ C
Temperature Coefficient	± 400 ppm/ $^{\circ}$ C

Electrical Characteristics

Operating Voltage	500 V
Power Rating	5 W
Resistance Class	Up to 1k Ω
Resistance Value	15 Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound, Ceramic Composition

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	17.5 x 6.5 mm
------------------------------	---------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on [TE.com](https://www.te.com/compliance)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2176081-7
EP 1W (S) 100R 5%TE Part # 2176085-7
EP 9W (S) 100R 5%TE Part # 2176083-1
EP 5W (S) 10R 5%TE Part # 2176045-3
EP 5W 15R 5%TE Part # 2176084-7
EP 7W (S) 100R 5%TE Part # 2176079-5
EP 3W 47R 5%


Also in the Series | Neohm EP



Through-Hole Resistors(607)

Customers Also Bought

TE Part #2-2172091-2
M8.FMLE.PNLREAR.3POS.PCBSTAND.RA.SHLDTE Part #147721-3
04 MODII HORZ SR SFMNT 30AUTE Part #1676192-2
RN 0805 14K 0.1% 10PPM 1KRLTE Part #1676264-3
RN 0805 249R 0.1% 10PPM 5KRL



Documents

Product Drawings

EP 5W (S) 15R 5%

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2176083-2_BA1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176083-2_BA1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176083-2_BA1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Wirewound Anti Surge Resistors - Type EP Series

English