

# CA-1RS1N8A2S00 - Device connector front mounting



1624015

<https://www.phoenixcontact.com/us/products/1624015>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 16+2+FE, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, Flat gasket, 4x Ø 3.2, flange dimensions: 25 mm x 25 mm, coding: N

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

Item number	1624015
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEL
Catalog page	Page 101 (C-2-2019)
GTIN	4055626228198
Weight per piece (including packing)	26.4 g
Weight per piece (excluding packing)	22.7 g
Customs tariff number	85366990
Country of origin	DE

# CA-1RS1N8A2S00 - Device connector front mounting



1624015

<https://www.phoenixcontact.com/us/products/1624015>

## Technical data

### Notes

Order information:	Order crimp contacts 16 x Ø 1 mm, 3 x Ø 1.5 mm separately
--------------------	-----------------------------------------------------------

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Material specifications

Flammability rating according to UL 94	V0
----------------------------------------	----

### Connector

#### Insulating body

Note	Order information: Order crimp contacts 16 x Ø 1 mm, 3 x Ø 1.5 mm separately
Coding	N
Insulation body material	PA 6.6
Insertion/withdrawal cycles	100
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+2+FE
Contact diameter	1.5 mm
<b>Power contacts</b>	
Litz wire cross-section	Power contacts min. 0.08 mm <sup>2</sup>
Litz wire cross-section	Power contacts max. 1 mm <sup>2</sup>
Rated current	Power contacts 10 A
Note	for max. connection cross section
Rated voltage	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	II
Degree of pollution	3
Contact diameter	Signal contacts 1 mm
Litz wire cross-section	Signal contacts min. 0.08 mm <sup>2</sup>
Litz wire cross-section	Signal contacts max. 1 mm <sup>2</sup>
Nominal current per signal contact	8 A
Note	for max. connection cross section
Rated voltage	Signal contact 48 V AC
Rated surge voltage	1.5 kV

# CA-1RS1N8A2S00 - Device connector front mounting



1624015

<https://www.phoenixcontact.com/us/products/1624015>

Overvoltage category	III
Degree of pollution	3
Installation height	2000 m

## Housing

Housing material	GD-Zn
Flange dimensions	25 mm x 25 mm
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23


## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

## Drawings

Dimensional drawing




Installation dimensions

1624015

<https://www.phoenixcontact.com/us/products/1624015>

Schematic diagram



Connector pin assignment

# CA-1RS1N8A2S00 - Device connector front mounting





1624015

<https://www.phoenixcontact.com/us/products/1624015>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1624015>

 <b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
Power	48 V	6 A	18 - 18	-
Signal	48 V	5 A	18 - 18	-

 <b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
Power	48 V	10 A	18 - 18	-
Signal	48 V	8 A	18 - 18	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# CA-1RS1N8A2S00 - Device connector front mounting



1624015

<https://www.phoenixcontact.com/us/products/1624015>

## Classifications

### ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

### ETIM

ETIM 9.0	EC003569
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-1RS1N8A2S00 - Device connector front mounting



1624015  
<https://www.phoenixcontact.com/us/products/1624015>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)