

1394429-2

✓ ACTIVE


MAG-MATE

TE Internal #: 1394429-2

RAST 5D, .18 – .27 mm Magnet Wire, 33 – 31 AWG Magnet Wire,
Insulation Displacement (IDC), Tin Plating, MAG-MATE, Magnet
Wire Terminals

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals

Magnet Wire Terminal Type: **RAST 5D**Magnet Wire Size: **.18 – .27 mm**Termination Method to Wire & Cable: **Insulation Displacement (IDC)**Stock Thickness (Magnet Wire Side): **.32 mm [.013 in]****Features****Usage Conditions**

Insulation Option	Uninsulated
-------------------	-------------

Dimensions

Terminal Height	16.2 mm[.637 in]
Magnet Wire Size	.18 – .27 mm
Stock Thickness (Magnet Wire Side)	.32 mm[.013 in]
Product Length	16.2 mm[.637 in]

Product Type Features

Compatible With Discrete Wire Type	Solid, Magnet Wire
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	RAST 5D
Terminal Plating Material	Tin
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel/Carton
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | **MAG-MATE**



Insertion & Extraction Tools(6)



Magnet Wire Terminals(329)



PCB Terminals(1)

Customers Also Bought

TE Part #2-1393243-4
RTE25524TE Part #1623187-1
CRG0805 1% 300KTE Part #1825142-2
AE101MD1AG04TE Part #7-1393238-2
RTD14110TE Part #9-1879256-5
RP 2B 237R 0.1% 15PPM 1K RLTE Part #964339-1
MAG MATE KONT. MKIITE Part #1-1546111-0
EUROSTYLE TB,HEADER,GRAY,10POSTE Part #5822138-4
80 ME .050 L/P AU M/L PB-FREETE Part #9-2176374-8
RQ 0805 1K1 0.1% 10PPM 1K RL

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_1394429-2_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1394429-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1394429-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English