



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Guide Pin Module**

Primary Product Material: **Stainless Steel**

Hardware Accessory Function: **Guide Hardware**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Dimensions

Thread Length	7.5 mm[.295 in]
---------------	-----------------

Mechanical Attachment

Thread Size	M4 x 0.7-6G
Product Plating Finish	Passivated

Packaging Features

Packaging Method	Box
Packaging Quantity	1000

Body Features

Product Orientation	Vertical
Primary Product Material	Stainless Steel

Product Type Features

Connector Hardware Accessory Type	Guide Pin Module
Hardware Accessory Function	Guide Hardware

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5223957-3
[UPM GUIDE MODULE](#)


Customers Also Bought




TE Part #2-5499206-6
A/L UNIV HDR 26P VERT LG LAT BLUE



TE Part #5188578-1
Z-PACK/A M HDR.154P



TE Part #120954-1
TE UPM R/A Header 4P HC Power, LLLL




TE Part #647878-1
SERIES 50 & 75 CONTACT,8 AWG



TE Part #63698-1
FASTON .187 (4.75 MM) ADAPTER TPBR




TE Part #2176326-3
CRGP 0603 15R 1%




TE Part #2331813-2
CABLE REC ASSY, 84 P, VERT, SLIVER 2.0



TE Part #1-776279-1
8POS,PIN DIA 1.3,HDR ASSY,90DEG, COD 1



TE Part #2379397-7
MCIO INTERGRATED CONN, V/T,8X, SMT TYPE



TE Part #2176550-1
RLW73P A3 1% R010 600ppm 4k RL

Documents

Product Drawings
Stainless Steel Guide Pin M4x0.7
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_223982-1_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_223982-1_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_223982-1_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



[High Speed Backplane Connectors catalog - Z-PACK HS3 Connector](#)

English

[POWER_CONNECTORS_CATALOG_SEC01_BOARD_TO_BOARD](#)

English

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

[Product Specifications](#)

[Engineering Report](#)

English