


Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules

Crimp Wire Terminal Type: **Pin**Compatible Insulation Diameter Range: **2.67 – 3.56 mm [.105 – .14 in]**Wire Size: **.25 – 1.6 mm²**Barrel Type: **Closed**

Features

Operation/Application

Compatible With Wire Plating Material	Tin
Compatible With Wire Base Material	Copper

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Type Features

Wire Insulation Support Retention Type	Insulation Support
--	--------------------

Contact Features

Crimp Wire Terminal Type	Pin
Barrel Type	Closed
Terminal Plating Material	Tin
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter Range	2.67 – 3.56 mm [.105 – .14 in]
--------------------------------------	--------------------------------

Wire Size	.25 – 1.6 mm ²
-----------	---------------------------

Overall Product Length	20.14 mm [.793 in]
------------------------	--------------------

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Other

EU RoHS Compliance	Compliant
--------------------	-----------

EU ELV Compliance	Compliant
-------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)
--	--

	Candidate List Declared Against: JUNE 2024 (241)
--	--

	Does not contain REACH SVHC
--	-----------------------------

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 567200-3
APPL,HDM,TAPE 9CB W/O DIES G




TE Part # 687658-1
APPL,HDM,TAPE 9 CB W/O DIES T

Also in the Series | STRATO-THERM



Crimp Wire Pins, Tabs & Ferrules(1)



Ring Terminals(85)



Splices(13)

Customers Also Bought



TE Part #413985-1
PLUG ASSY,STR,SMB



TE Part #5188232-1
2MMHM PIN HDR MOD C 55 POS



TE Part #487526-3
004 HOUSING FFC RCPT 100CL SR



TE Part #487406-2
FFC RCPT CONT SP 30AU RL



TE Part #1-1757823-2
AMPLIMITE,ASY,PLUG,STD,90,ZN,6,CT



TE Part #165075
P.G. WIRE PIN 16-14



TE Part #A75939-000
HX-SCE-1K-2.4-50-S1-9



TE Part #CAT-T3437-ST2999
STD Snap-On Markers



TE Part #1241962-1
SPT REC 6.3 Contact SWS Sn

Documents

Product Drawings

[TERM, WIRE PIN, PIDG, 22-16, T&R](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_696153-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_696153-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_696153-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.