



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**

Strain Relief: **With**

Primary Product Color: **Black**

Primary Product Material: **PBT GF**

EU RoHS Compliance: **Compliant**

Features

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Dimensions

Compatible Cable Bundle Diameter Range	16.8 mm[.661 in]
----------------------------------------	------------------

Packaging Features

Packaging Method	Box
Packaging Quantity	1000

Other

Serviceable	Yes
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Type Features

Protection & Strain Relief Accessory Type	Cover
-------------------------------------------	-------

Mechanical Attachment

Strain Relief	With
---------------	------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1719675-1
32 POS MIXED REC HSG



TE Part # 1-2177515-7
32POS, MIXED,REC HSG,ASSY, SEALED



TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

Customers Also Bought



TE Part #1394871-1
MQS Dichtstopfen



TE Part #2371242-3
CU Alloy, Inner Ferrule, ICT CVE



TE Part #2371244-3
SWS, Dia 4mm, ICT CVE



TE Part #347887-3
2 Way Junior Timer Conn.



TE Part #CAT-M8793-CH8172
MQS, Connector Housing



TE Part #1-2287018-3
TAB 9.5x1.2, 6sqmm, AG



TE Part #1-2294256-1
4POS, MCON 1.2 LL REC SEALED



TE Part #1670108-1
Blind Plug Female 1.5



TE Part #2290490-1
16POS, 1.0 Series, REC HSG Assy, SLD

Documents

Product Drawings

COVER MQS CB 90

English

CAD Files

Customer View Model

ENG_CVM_CVM_1719667-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1719667-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1719667-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English