



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable**

Number of Positions: **37**

Power/Signal/Coax Combination: **No**

Connector Shell Size: **4**

Features

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Body Features

Front Shell Material	Steel
Mating Retention Feature Material	Stainless Steel
Rear Shell Plating Material	Cadmium
Rear Shell Material	Steel
Front Shell Plating Material	Cadmium

Packaging Features

Packaging Method	Package
------------------	---------

Mechanical Attachment

Connector Mounting Type	Panel Mount
Mounting Hole Diameter	3.05 mm[.12 in]
Mating Alignment	Without

Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Options	Supplied – Uninstalled
Contact Type	Pin



Contact Size	Size 20
Contact Current Rating (Max)	7.5 A

Product Type Features

Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Connector Shell Size	4
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	37
Power/Signal/Coax Combination	No

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 601966-1
CRIMPING TOOL M22520/2-01




TE Part # 601966-5
K13-1 POSITIONER


Customers Also Bought




TE Part #205560-2
AMPLIMITE,ASY,PLUG,STD,109,3




TE Part #5748676-4
DIE CAST CBL CLMP KIT,SZ 4




TE Part #1487594-1
USB, A-B, 28/28, BLACK, 0.5M




TE Part #4-2176306-6
RP 1E 0.1W 3K4 0.1% 25PPM 5K RL




TE Part #382432-011
44A1121-18-0/9-9



TE Part #205564-3
AMPLIMITE,ASY,PLUG,STD,109,5,KIT



TE Part #NB-PTCO-295
Pt1000, 2.0x2.3, Class B, PTFC102BC1G0



TE Part #1757820-8
AMPLIMITE,ASY,RCPT,STD,109,ZN,3,CT



TE Part #1532174-3
M83513/04-D03N, MCKS-N1-B-25S6G9-18.0



TE Part #2176250-6
TJT 500W 6R8 5%

Documents

Product Drawings

AMPLIMITE,ASY,PLUG,STD,109,4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_205562-2_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_205562-2_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_205562-2_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.