

32859 ✓ ACTIVE

SOLISTRAND | SOLISTRAND Budget

TE Internal #: 32859

Closed Ring Tongue Terminal, 26 AWG, #8 / M4 Stud, 4.17 mm [.


164 in] Stud Diameter, Closed Barrel, Straight, Tin Plating,

SOLISTRAND Budget

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **202 – 810 CMA**

Stud Size: **#8, M4**

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Other

Line	Budget
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4

Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	4.17 mm [.164 in]
Tongue Thickness	.51 mm [.02 in]
Product Length	13.82 mm [.544 in]
Barrel Inside Diameter	.89 mm [.035 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | SOLISTRAND Budget



Customers Also Bought



TE Part #1466110-1
13201140002TE Part #015312380798-M
CD-375-500-0798TE Part #11190381-00
150PSI, 1/2MNPT, 4-20MA, 316L, 10FT
HYTRTE Part #YDTS24H13-35ZN0000
HERM RECP ASSYTE Part #YDTS24H15-35ZN0000
HERM RECP ASSY

Documents

Product Drawings

TERMINAL,BUDG R 26-22 8

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_32859_AY.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_32859_AY.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_32859_AY.3d_stp.zip](#)

English

Datasheets & Catalog Pages

SOLISTRAND - QRG

English