


EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters



Current Rating: **6 A**

Input Termination Type: **.250" FASTON**

Output Termination Type: **.250" FASTON**

Wiring Configuration: **WYE (4 wire + ground)**

Operating Voltage: **440 VAC**

## Features

### Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------

### Product Type Features

Filtering Requirements	Filtered
Input Termination Type	.250" FASTON
Output Termination Type	.250" FASTON

### Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	3
Current Rating	6 A
Operating Voltage	440 VAC

### Configuration Features

Wiring Configuration	WYE (4 wire + ground)
----------------------	-----------------------

### Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | [Corcom KES](#)



3-Phase Filters(38)

## Customers Also Bought



TE Part #1-1337463-0  
BNC Plg Term 50Ohm Silver Pltd



TE Part #NB17592001  
RT-375-3/4-X-STK



TE Part #6609066-2  
6AY01=F7692 S0

## Documents

### Product Drawings

#### KES 6A 1S SPADE WYE 440VAC

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1609966-2\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1609966-2\\_B.3d\\_stp.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1609966-2\\_B.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### KES SERIES

English