



CII

TE Internal #: 1-1617542-7

General Purpose Signal Relay, DC, Non-Polarized, Monostable, 2 Form C DPDT-CO, 1 A Contact Rating, 12 VDC Coil Voltage, .369 W Coil Power, Board Mount

[View on TE.com >](#)

Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Signal Relay**

Current Type: **DC**

Coil Magnetic System: **Non-Polarized, Monostable**

Contact Arrangement: **2 Form C DPDT-CO**

Contact Current Rating: **1 A**

Features

Usage Conditions

Operating Temperature Range	-65 – 125 °C
Environmental Ambient Temperature (Max)	125 °C[257 °F]

Electrical Characteristics

Coil Resistance	390 Ω
Contact Switching Voltage (Max)	28 VDC
Contact Current Rating	1 A
Coil Voltage Rating	12 VDC
Coil Power Rating DC	.369 W

Configuration Features

Coil Special Features	Coil Suppression Diode
Pin Configuration	.200" x .300" Spreader Pad
Relay Options	Transistor Driver
Contact Arrangement	2 Form C DPDT-CO

Operation/Application

Vibration Resistance	30G's, 10 – 3000Hz
Shock Resistance	75G's, 6ms
Current Type	DC



Coil Magnetic System	Non-Polarized, Monostable
Product Type Features	
Relay & Contactor Type	General Purpose Signal Relay
Body Features	
Enclosure Type	Hermetically Sealed
Termination Features	
Main Termination & Connection Type	Extended Leads
Coil Termination & Connection Type	Extended Leads
Mechanical Attachment	
Product Mount Type	Board Mount
Other	
EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An



Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2-1617030-7
HFW1201G01M = M39016/6-116M

Customers Also Bought



TE Part #1617005-5
B07D992BB2-0117 = M5757/23-007



TE Part #1617167-7
JMSCDD-26XPS = M39016/21-046P



TE Part #1-1423152-0
2112DH3NE=RLY,MINI,ON,2P,HERM



TE Part #1-1617168-3
JMSCT-26XPS = M28776/3-046P



TE Part #4-1617514-0
3SAT1338A2=M5757/13-121



TE Part #3-1617118-0
J1MACDD-12XP = M39016/24-028P



TE Part #1-1616037-6
DHR7B=CONTACTOR - 3PDT



TE Part #1616021-6
SA136A=CONTACTOR 3PST N.O. 75



TE Part #3-1617536-2
HFW1230F01P=M39016/6-119P



TE Part #1-1618273-5
H-16C=RELAY, VACUUM, DPDT

Documents

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-1617542-7_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1617542-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1617542-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec1_MAT](#)

English