



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**  
Primary Product Material: **Thermoplastic**  
Primary Product Color: **Black**  
Compatible With Connector Shell Size: **11**  
Cable Entry Diameter: **8.36 mm [ .329 in ]**

Features

Housing Features

|                                 |          |
|---------------------------------|----------|
| Compatible With Connector Shape | Circular |
| Body Orientation                | Straight |

Product Type Features

|                              |                 |
|------------------------------|-----------------|
| Strain Relief Accessory Type | Cable Clamp Kit |
|------------------------------|-----------------|

Body Features

|                          |               |
|--------------------------|---------------|
| Primary Product Material | Thermoplastic |
| Primary Product Color    | Black         |

Operation/Application

|                                      |    |
|--------------------------------------|----|
| Compatible With Connector Shell Size | 11 |
| Shielded                             | No |

Dimensions

|                      |                  |
|----------------------|------------------|
| Cable Entry Diameter | 8.36 mm[.329 in] |
|----------------------|------------------|

Mechanical Attachment

|             |                |
|-------------|----------------|
| Thread Size | 5/8-24 UNEF-2B |
|-------------|----------------|



Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                    |            |
|--------------------|------------|
| Packaging Method   | Individual |
| Packaging Quantity | 1          |

Other

|                    |           |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance  | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.  |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-206062-4  
CABLE CLAMP KIT #11

Also in the Series | AMP CPC



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)



Power Contacts(6)

Customers Also Bought



TE Part #205210-8  
PLUG ASSY SIZE 4



TE Part #205205-7  
CRIMP SNAP RCPT ASSY,SIZE 2



TE Part #5205207-1  
HD RECPT ASSY SIZE 3




TE Part #205838-1  
CPC PLUG ASSEMBLY SIZE 11-8



TE Part #206430-2  
CPC 11-4 Free Hanging Receptacle



TE Part #206485-1  
CPC PLUG ASSEMBLY SIZE 11-9



TE Part #206358-5  
CABLE CLAMP ASY, SIZE 11



TE Part #66361-3  
III+ PIN,18-14,15AU/FL,LP



Documents

Product Drawings

CPC cable clamp, size 11

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1-206062-3\_W.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-206062-3\_W.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-206062-3\_W.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English