


1-327743-1 ACTIVE**PIDG**

TE Internal #: 1-327743-1

Closed Ring Tongue Terminal, 16 – 14 AWG, M6 Stud, 6.73 mm [.
265 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially
Insulated

[View on TE.com >](#)[Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals](#)Ring Terminal Product Type: **Closed Ring Tongue Terminal**Wire Size: **2050 – 5180 CMA**Stud Size: **M6**[All PIDG Ring Tongue Terminals \(410\)](#)**Features****Configuration Features**

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Product Weight	.611 g
----------------	--------

Stripe Color	Black
--------------	-------

Packaging Features

Packaging Quantity	1
--------------------	---

Packaging Method	Tape Mounted
------------------	--------------

Product Type Features

Terminal Features	Heavy Duty
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M6
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	6.73 mm [.265 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	1.3 mm [.051 in]
Compatible Insulation Diameter (Max)	5.84 mm [.23 in]
Compatible Insulation Diameter Range	3.81 – 5.84 mm [.15 – .23 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE
2024 (241)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 59239-4
HHT PIDG PG 12-10 ASSY



TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY



TE Part # 169404
CERTI-LOK DIE




TE Part # 58423-1
DIE, RBY IS9252



TE Part # 58433-3
PRO CR ASSY, RBY IS9252


Also in the Series | PIDG




Compression Connectors(17)




Crimp Wire Pins, Tabs & Ferrules(41)




Hand Crimping Tools(2)




Knife Disconnects(11)




Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(41)

Customers Also Bought

TE Part #440129-2
2.0MM,HSG,2POSTE Part #350783-1
12P UMNL CAP HSGTE Part #1-480701-0
03P UMNL CAP HSG NATLTE Part #1-480700-0
03P UMNL PLUG HSG NATLTE Part #770903-1
MINI UMNL PIN 22-18 AWG SNTE Part #1735801-1
2.0mm,Crimp,ContactTE Part #770904-1
MINI UMNL SOK 22-18 AWG SNTE Part #42660-2
250 FASTON REC 18-14 AWG TPBR

TE Part #2119582-2
Crimper, Insulation F PremiumTE Part #3-1333201-0
ANVIL, COMBINATION (.055)

Documents

Product Drawings

TERMINAL,PIDG R 16-14HD 1/4

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-327743-1_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-327743-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-327743-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English