

CONSMA013.031-G

✓ ACTIVE

TE Internal #: L9000274-01
SMA Connector, Plug, 50 ohm, Threaded, 0 – 18 GHz, 1 Position,
Printed Circuit Board, Board Mount, -65 – 165 °C [-85 – 329 °F],
Solder, Straight
[View on TE.com >](#)



Connectors > RF Connectors > Coax Connectors



RF Interface: **SMA**
RF Connector Style: **Plug**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Threaded**
Operating Frequency: **0 – 18 GHz**

Features

Packaging Features

Packaging Quantity	100
Packaging Method	Tray

Configuration Features

PCB Mount Orientation	Edge
Number of Positions	1
Number of Coaxial Contacts	1

Operation/Application

Circuit Application	Signal
Operating Frequency	0 – 18 GHz

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	SMA
RF Connector Style	Plug
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Electrical Characteristics

Impedance	50 Ω
-----------	------



Mechanical Attachment

RF Connector Coupling Mechanism	Threaded
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Material Finish	Plated
Body Plating Material	Gold

Contact Features

RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Other

Dielectric Material	PTFE
EU RoHS Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 2480662-1 SMA F St BHD to Open Semi-rigid.047 50mm	TE Part # L9000271-01 SMA Jack 50 Ohm .062 PCB Edge Mount	TE Part # CON SMA001-SMD SMA Jack 50 Ohm PCB Surface Mount	TE Part # CON SMA017-1 SMA Jack 50 Ohm Panel Mount
TE Part # CON SMA014-R178 SMA Jack 50 Ohm Cable Crimp Panel Mount	TE Part # CON SMA002-SMD SMA Jack 50 Ohm PCB Surface Mount	TE Part # CON SMA001-SMD-G-T SMA Jack 50 Ohm PCB Surface Mount	TE Part # CON SMA001-SMD-G SMA Jack 50 Ohm PCB Surface Mount
TE Part # CON SMA002-L SMA Jack 50 Ohm PCB Through Hole	TE Part # CON SMA017-2 SMA Jack 50 Ohm Panel Mount	TE Part # CON SMA022-G SMA Jack 50 Ohm PCB Edge Mount	TE Part # L9000279-01 SMA Jack 50 Ohm .062 PCB Edge Mount

CONSMA013.031-G

SMA Connector, Plug, 50 ohm, Threaded, 0 – 18 GHz, 1 Position, Printed Circuit Board, Board Mount, -65 – 165 °C [-85 – 329 °F], Solder, Straight



TE Part # L9000264-01
SMA Jack 50 Ohm .031 PCB Edge Mount



TE Part # CONSMA015
SMA Jack 50 Ohm Cable Crimp Panel Mount



TE Part # CONSMA015-R178-G
SMA Jack 50 Ohm Cable Crimp Panel Mount



TE Part # L9000266-01
SMA Jack 50 Ohm .062 PCB Edge Mount



TE Part # L9000268-01
SMA Jack 50 Ohm .062 PCB Edge Mount



TE Part # L9000267-01
SMA Jack 50 Ohm .062 PCB Edge Mount gold



TE Part # L9000263-01
SMA Jack 50 Ohm .031 PCB Edge Mount



TE Part # CONSMA016-15-G
SMA Jack 50 Ohm Panel Mount

Customers Also Bought



TE Part #M3021-000005-100PG
PRESS XDCR M3021-000005-100PG



TE Part #5-794630-2
22P MICRO MNL ASSY,VRT,HDR,LF



TE Part #5-1625868-6
RP 2A 0.25W 20R 0.1% 25PPM 1K RL



TE Part #2439034-2
Vertical USB 3.2 A (board lock) / Au15uM



TE Part #CONMCX001-SMD
MCX Jack 50 Ohm PCB Surface Mount



TE Part #CONSMA002-L
SMA Jack 50 Ohm PCB Through Hole



TE Part #L9000276-01
SMA Plug 50 Ohm .062 PCB Edge Mount



TE Part #L9000277-01
SMA Jack 50 Ohm .031 PCB Edge Mount



TE Part #L9000279-01
SMA Jack 50 Ohm .062 PCB Edge Mount



TE Part #CSC-BNCM-1800-BNCM
BNC to BNC 1800mm RG58

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_L9000274-01_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_L9000274-01_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_L9000274-01_A.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMA MALE EDGE MOUNT FOR 0.031INCH BOARD

English