

VC-MP-K1 - Housing

1884568

<https://www.phoenixcontact.com/us/products/1884568>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing, Range of articles: VARIOCON, design: VC1, housing material: Die-cast zinc, color: gray, When using fiber optics, the bending radii of the cable manufacturers must be observed.

Your advantages

- Any position can be a PE contact

Commercial data

Item number	1884568
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB01
Product key	ABLADB
Catalog page	Page 31 (C-2-2013)
GTIN	4017918164591
Weight per piece (including packing)	369.76 g
Weight per piece (excluding packing)	352 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Notes

General	When using fiber optics, the bending radii of the cable manufacturers must be observed.
General	The coupling housings may not be used in combination with the VC-D... contact carriers

Safety note

Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
	• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
	• The products are suitable for applications in plant, controller, and electrical device engineering.
	• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.
	• Assembled products may not be manipulated or improperly opened.
	• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
	• When using the product in direct connection with third-party manufacturers, the user is responsible.
	• For operating voltages > 50 V AC, conductive connector housings must be grounded
	• Ensure that the protective or functional ground has been properly connected.
	• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector
	• Observe the corresponding technical data. You will find information: - o On the product - o On the packing label - o In the supplied documentation - o Online at phoenixcontact.com/products under the product
	• Only use tools recommended by Phoenix Contact
	• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
	• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory

VC-MP-K1 - Housing

1884568

<https://www.phoenixcontact.com/us/products/1884568>



section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Operate the connector only when it is fully plugged in.

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.


- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Sleeve housings
Product family	VARIOCON
Type	VC1
No. of cable outlets	1
Number of module slots	2
Type of the screw connection	1x Pg16
Shielded	no
Cable outlet	lateral

Dimensions

Dimensional drawing	
Width	36.4 mm
Height	61 mm
Length	62.6 mm
Thread type on seal side	Pg16

Material specifications

Color	gray
Color of the housing part	gray
Material	Die-cast zinc (Housing)
Housing material	Die-cast zinc
O-ring material	NBR

Mechanical properties

Mechanical data	
Type of the screw connection	1x Pg16
Locking type	Nut

Environmental and real-life conditions

Ambient conditions

VC-MP-K1 - Housing

1884568

<https://www.phoenixcontact.com/us/products/1884568>



Degree of protection	IP65/IP66/IP67
Ambient temperature (operation)	-40 °C ... 125 °C

VC-MP-K1 - Housing


1884568

<https://www.phoenixcontact.com/us/products/1884568>



Drawings

Dimensional drawing



VC-MP-K1 - Housing

1884568

<https://www.phoenixcontact.com/us/products/1884568>



Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

VC-MP-K1 - Housing

1884568

<https://www.phoenixcontact.com/us/products/1884568>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com