

DDR4 DIMM

TE Internal #: 2309407-2

Small Outline (SO), Stack Height 4 mm [.157 in], Right Angle

Module Orientation, 260 Position, .5 mm [.02 in] Centerline, DDR4

DIMM, SO DIMM Sockets

[View on TE.com >](#)



Connectors > Socket Connectors > Memory Sockets > SO DIMM Sockets > DDR4 SO DIMM Sockets



DRAM Type: **Small Outline (SO)**

Stack Height: **4 mm [.157 in]**

Module Orientation: **Right Angle**

Number of Positions: **260**

Centerline (Pitch): **.5 mm [.02 in]**

[All DDR4 SO DIMM Sockets \(39\)](#)

Features

Electrical Characteristics

DRAM Voltage	1.2 V
--------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Insertion Style	Cam-In
Termination Method to PCB	Surface Mount

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention Type	Solder Peg
Mating Alignment Type	Standard Keying
PCB Mount Retention	With

Signal Characteristics

SGRAM Voltage	1.2 V
---------------	-------

Packaging Features

Packaging Quantity	900
--------------------	-----



Packaging Method	Tape & Reel
Contact Features	
Contact Current Rating (Max)	.5 A
Memory Socket Type	Memory Card
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold Flash
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.127 µm[5 µin]
Body Features	
Retention Post Location	Both Ends
Latch Material	High Temperature Thermoplastic
Module Key Type	Offset Left
Ejector Type	Locking
Ejector Location	Both Ends
Connector Profile	Low
Housing Features	
Housing Material	High Temperature Thermoplastic
Housing Color	Black
Centerline (Pitch)	.5 mm[.02 in]
Configuration Features	
Number of Keys	1
Number of Rows	2
Module Orientation	Right Angle
Number of Positions	260
Product Type Features	
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Cable-to-Board
DRAM Type	Small Outline (SO)
Dimensions	
Stack Height	4 mm[.157 in]
Row-to-Row Spacing	8.2 mm[.322 in]
Usage Conditions	



Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **DDR4 DIMM**



Customers Also Bought





Documents

Product Drawings

DDR4 SODIMM 260P 4.0H STD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2309407-2_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2309407-2_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2309407-2_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English