




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **3**
Terminal Orientation: **Straight**
Primary Product Color: **Natural**

Features

Dimensions

Product Length	20.4 mm[.803 in]
----------------	------------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Carton

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

--	--



Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Polyamide
------------------	-----------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 150653-1 FF 312 REC HSG 3P NYLON BLACK	 TE Part # 626213-1 FASTIN-ON 0.312 FLAG REC NYLON 6.6	 TE Part # 925176-5 FF 312 3P HOUSING REC POLYAMID 6.6 BLACK	 TE Part # 180918 FF 250 REC HSG 2P NYLON CLEAR
 TE Part # 170258-1 FF 250 REC 14-12AWG BR REREELING	 TE Part # 925015-1 FF 110 REC HSG 3P NYLON BLACK	 TE Part # 925306-2 FF 312 REC HSG 3P NYLON CLEAR	 TE Part # 1-172131-1 FF 250 CAP HSG 3P NYLON NAT
 TE Part # 927284-2 FF 250 REC HSG 3P NYLON NAT	 TE Part # 626213-2 3 CIR FASTIN-ON RECP HSG PRETO	 TE Part # 170258-2 FF 250 REC 14-12AWG TPBR REREELING	 TE Part # 925475-1 FF 110 REC HSG 3P NYLON NAT

Also in the Series | FASTIN-FASTON 250

 Crimp Terminal Housings(207)	 Insertion & Extraction Tools(2)	 PCB Terminals(2)	 Quick Disconnects(250)
---	--	---	---


Customers Also Bought



TE Part #1355390-1
JUN-POW-TIM GEH 2P



TE Part #926883-1
UNIVERSAL M-N-L PIN




TE Part #180453-2
FF 312 REC 1-2.5MM2 TPBR



TE Part #280095-2
FF 250 REC 0.3-0.8MM2 PTBR



TE Part #160684-4
FF 110 REC 0.5-1.0MM2 TPBR



TE Part #3-350566-1
MINI AMP-IN 22-18 PTLF/PHBZ



TE Part #5677654001
RNF-3000-9/3-2-SP



TE Part #1-962915-1
TAB 2.8x0.8 CONTACT CS SWS Sn



TE Part #828904-2
SINGLE WIRE SEAL FOR J.P.T.CON



TE Part #175022-1
250 PL EX REC. 18-14AWG PTBR

Documents

Product Drawings

FF 250 REC HSG 3P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_180913_AW.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_180913_AW.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_180913_AW.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English