



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cap**

Primary Product Color: **Black**

Primary Product Material: **Thermoplastic**

Operating Temperature (Max): **80 °C [176 °F]**

Operating Temperature Range: **-20 – 80 °C [-4 – 176 °F]**

Features

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Operation/Application

Compatible With Connector Shell Size	17
--------------------------------------	----

Product Type Features

Connector Cover Type	Protective Cap
----------------------	----------------

Body Features

Primary Product Color	Black
Primary Product Material	Thermoplastic

Usage Conditions

Operating Temperature (Max)	80 °C[176 °F]
Operating Temperature Range	-20 – 80 °C[-4 – 176 °F]

Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1776904-1
CPC POSTED RCPT,17-16,R/A

TE Part # 796112-1
CPC 17-3 RCPT ASY,REV SEX

TE Part # 211769-3
17-9 CPC RECEPT REV SEX

TE Part # 211767-1
17-9 CPC RECEPT

TE Part # 206038-1
CPC RCPT ASSEMBLY SIZE 17-28

TE Part # 1-207216-7
CPC RECEPT ASSEMBLY SIZE 17-28

TE Part # 213729-6
CPC RCPT ASSY,SZ 17-14,W/INSRT

TE Part # 211103-1
CPC RCPT ASSEMBLY 17-14



TE Part # 213855-3
CPC RECPT ASSEMBLY SIZE 17-16



TE Part # 206043-1
RECEPT,SZ 17-14 CPC



TE Part # 1-207303-3
CPC RECPT ASSEMBLY SIZE 17-16



TE Part # 796275-2
SLD CPC RCPT ASSY,17-16,STD SX



TE Part # 788189-2
CPC 17-3 RCPT ASY,REV SEX




TE Part # 1-207303-4
CPC RECPT ASSM SIZE 17-16



TE Part # 213893-2
CPC RECPT SEALED SIZE 17-10



TE Part # 206425-1
17-3 RECPT. REV SEX



TE Part # 1-796404-1
CPC PSTD RCPT,17-16,R/A LF



TE Part # 796276-1
SLD CPC RCPT ASSY,17-16,STD SX




TE Part # 206036-3
RECEPT,SZ 17-16,CPC



TE Part # 211769-1
17-9 CPC RECEPT REV SEX

Customers Also Bought



TE Part #CAT-EMIG-0003
Moulded EMI Gasket Conductive Sheet




TE Part #T4132012121-000
M12,FRONT MOUNT,MALE,A,12P, SOLDER WIRE



TE Part #66104-8
III+ SKT,24-20,15AU/FL,STRIP



TE Part #4-1393249-5
W58-XC4C12A-3=W58



TE Part #796273-1
SLD CPC RCPT ASSY,17-14,REV SX




TE Part #5677744002
RNF-3000-24/8-4-SP



TE Part #1SNG614006R0000
EM-EMC4-M32-MET-A



TE Part #364254-E
SRCBUG A 2,54 2 8 CSI 112 E1 ADV J 2 324



Documents

Product Drawings

CAP, CPC, SIZE 17 RECP, BLACK

English

CAD Files

Customer View Model

ENG_CVM_CVM_4-2407269-2_2.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_4-2407269-2_2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2407269-2_2.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English