

FX29K0-100A-0010-L

✓ ACTIVE

MEAS | MEAS FX29

TE Internal #: 20009605-20

TE Internal Description: FX29K0-100A-0010-L

Compact Compression Load Cell

[View on TE.com >](#)



Sensors > Force Sensors > Force Sensor Elements > Compact Compression Load Cell



Force Sensor Type: OEM Compression Load Cells

Full Scale Range: 10 lbf

Operating Temperature Range: 0 – 50 °C [ 32 – 122 °F ]

Output Signal Type: 14 Bit I2C

EU RoHS Compliance: Compliant with Exemptions

[All Compact Compression Load Cell \(46\)](#)

Features

Other

Sensitivity Shift	±.05 % of FS
Zero Shift in CTR	±.05 % of FS
Force Direction	Compression
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant

Usage Conditions

Accuracy	±1 % of FS
Operating Temperature Range	0 – 50 °C[32 – 122 °F]

Electrical Characteristics

Supply Voltage Range	3 VDC
Full Scale Range	10 lbf

Product Type Features

Force Sensor Type	OEM Compression Load Cells
-------------------	----------------------------

Operation/Application

Output Signal Type	14 Bit I2C
--------------------	------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | MEAS FX29




Force Sensor Elements(46)

Customers Also Bought



TE Part #211903-1  
CMC DUST CAP ASSM SIZE 22



TE Part #9-1879664-9  
H8 12K1 0.1% 15PPM



TE Part #CAT-FSE0006  
Compact Compression Load Cell




TE Part #2-1462041-6  
IMB06IGR=IM RELAY 140mW 12V




TE Part #T4113411051-000  
M12 M, 5P GOLD B\_CODE RA SHIELDED PG7



TE Part #1-292254-2  
CT RELAY HDR ASSY 12P NAT



TE Part #M3041-000006-100PG  
PRESS XDCR M3041-000006-100PG



TE Part #500-5760-00

Documents

Datasheets & Catalog Pages  
FX29 COMPRESSION LOAD CELL

English