



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Budget
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	10000
Packaging Method	Strip/Reel

Dimensions

Product Length	19.18 mm[.755 in]
Compatible Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150030-1
OCEAN_2.0_Applicator-E-090F130F-REM

TE Part # 346697-3
250 FASTON,REC.,20-16 AWG,PB

TE Part # 444334-3
250 FASTON REC 22-18 AWG BR

TE Part # 752856-1
DIES 90166-1

TE Part # 169400
CERTI-LOK FRAME W/O DIES

TE Part # 170304-2
250 FASTON,REC.,22-18 AWG,BR

TE Part # 1494217-1
110 FASTON,REC.,18-22 AWG,PB

TE Part # 7-2150030-7
OCEAN_2.0_SPARE_PART_KIT-090F130F

TE Part # 2150030-2
OCEAN_2.0_Applicator-E-090F130F-REA

TE Part # 444334-2
250 FASTON REC 22-18 AWG TPBR

Also in the Series | **FASTON 250**



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(425)



Splices(4)

Customers Also Bought



TE Part #2-2176057-7
RLP73K 3A R12 1% 1K RL



TE Part #213847-4
PWRBND SOC ASY,14-12,L.P.




TE Part #ANT-433-CW-RH-SMA
Antenna 1/4 Wave Short 433MHz SMA



TE Part #1924678-1
26P SMT LAC HDR ASY, KEY AE, Hand Mate



TE Part #1924141-1
Shield, 26P GenY, Hand Mate Conn



TE Part #1924955-1
CONTACT,FEMALE0.64,20-22AWG, UNSEAL




TE Part #1924136-3
Carrier, 26P GenerationY, Hand Mate Conn



TE Part #HUM-900-PRC-CAS
Module HUM-PRC 900MHz FHSS FM XCVR FCC



TE Part #1-1414939-4
V23130C2021A412-EV-CBOX



TE Part #2844940-4
AIR FEED MODULE (EF-50MM)

Documents



Product Drawings

250 FASTON REC 22-18 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_42510-1_AH.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42510-1_AH.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42510-1_AH.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English