




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	Without
Mating Retention Type	Dimple

Packaging Features

Packaging Quantity	2500
Packaging Method	Strip/Reel

Dimensions

Product Length	16.26 mm[.64 in]
----------------	------------------



Terminal Material Thickness	.46 mm[.018 in]
Wire Size	.82 – 2.08 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 62048-2 250 FASTON REC 18-14 AWG TPBR	 TE Part # 63011-2 250 FASTON FLAG REC 18-14 AWG TPBR	 TE Part # 63012-2 250 FASTON FLAG REC 18-14 AWG TPBR	 TE Part # 63647-1 250 FASTON FLAG REC 18-14 AWG BR
 TE Part # 61187-1 250 FASTON FLAG REC 12-10 AWG PHBZ	 TE Part # 2232111-1 250 FASTON,FLAG,REC.,12-20 AWG, TPBR	 TE Part # 61188-1 250 FASTON FLAG REC 16-12 AWG TPBZ	 TE Part # 60764-2 250 FASTON FLAG REC 18-14 AWG TPBR
 TE Part # 63137-1 250 FASOTN FLAG REC 20-16 AWG TPBZ	 TE Part # 62811-2 250 FASTON FLAG REC 18-14 AWG TPBR		

Also in the Series | **FASTON 250**




Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(425)



Splices(4)

Customers Also Bought



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #DT06-6S-CE13
PLG, 6P, BLK, E, SEAL RET, XCAP




TE Part #2176230-2
3522 1R0 5% 3W



TE Part #1622385-1
LR1 1% 220K



TE Part #282191-1
SPLASH PROOF CONN. W.S.L.




TE Part #2-929939-1
JPT REC 2.8 Contact SWS Au



TE Part #DT12-L012-GKT
GASKET DT 12 WY FLD RC



TE Part #1062-12-0144
SOC, SF, SIZE 12, 12-14, AU/SN



TE Part #2217412-2
GUIDE, SHEAR

Documents



Product Drawings

250 FASTON FLAG REC 18-14 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63647-3_V.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63647-3_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63647-3_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Engineering Report

English