



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: Optic Compatible, Thermal Protection, Not Dimmable, Not Programmable, Driver on Board, Enables Zhaga Compatibility

Operating Voltage: 48 VDC

Termination Method to Wire & Cable: Mini CT Connector

Connector System: Wire-to-Device

Number of Positions: 2

Features

Housing Features

Housing Material	PBT
------------------	-----

Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy

Product Type Features

COB Substrate Thickness	1 mm
LED Holders Product Type	LED Holder
Connector System	Wire-to-Device

Configuration Features

Lighting Connector Features Included	Optic Compatible, Thermal Protection, Not Dimmable, Not Programmable, Driver on Board, Enables Zhaga Compatibility
Number of Positions	2

Electrical Characteristics



Operating Voltage	48 VDC
-------------------	--------

Termination Features

Termination Method to Wire & Cable	Mini CT Connector
------------------------------------	-------------------

Other

EU RoHS Compliance	Compliant with Exemptions
--------------------	---------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought



TE Part #1-440055-1
2.0MM,HDR,11POS,R/A

TE Part #8-2176407-8
3560 27R 5%

TE Part #4-2176414-8
7W STD M/OX 5% 1K8

TE Part #4-1879350-2
RR01 5% 11R AMMO

TE Part #1-1415899-8
RZ03-1A4-D048

TE Part #1623804-8
SQZ10 3R3 5% WIRE

TE Part #TAA545B1411-060
M12A4-MS-FS-PVC-6.0M

TE Part #8-1419125-5
SDT-S-106LMR,000

TE Part #1-1393250-7
W28-XQAT-15=W28

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2213699-3_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2213699-3_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2213699-3_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE Drive LED Holder Type Z50 Presentation

English

Product Specifications



Application Specification

English

Application Specification

English

Agency Approvals

UL Report

English