




Connectors > Connector Accessories > Connector Hardware



Operating Temperature (Max): 105 °C [221 °F]

Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-035-DCRSS201
D-Sub Crimp Recpt Signal 9 Posn,
Socket Size 20, Shell Size 1



TE Part # 2169638-1
KIT,HDP-20,RCPT,SIZE 1




TE Part # 1-966830-1
HD20 CONNECTOR KIT

Customers Also Bought



TE Part #5747460-5
HD-20 RCPT 15P RA 590 FFSCRLK



TE Part #5747841-2
15 MSFL PLUG RA 318 (FM,BL)



TE Part #749805-8
KIT,HDP-20,PLUG,SIZE 2, 15 POS



TE Part #207526-9
SKT HDR ASSY,9P,MMATE LF



TE Part #5055556-9
10 POWER TAP ASSY .125



TE Part #120958-1
UPM EXPANDED PIN ASSEMBLY



TE Part #4-1617758-8
FCB-205-0223M=M83536/2-023M



TE Part #205090-2
SKT CONT ASSY,SZ 20,AMPLIMITE



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_747521-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_747521-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_747521-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.