




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**
Wire Size: **592 – 3260 CMA**
Mating Tab Width: **2.79 mm [.11 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Body Features

Insulation Material	Nylon
---------------------	-------

Other

Barrel Color	Red
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	1000
Packaging Method	Loose Piece

Dimensions

Product Length	19.8 mm[.779 in]
Compatible Insulation Diameter Range	3.5 mm[.14 in]
Wire Size	592 – 3260 CMA

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.79 mm[.11 in]
Mating Tab Thickness	.41 mm[.016 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Compression Crimp
Barrel Type	Closed

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 525690 DAHT PG PIDG 20-18 ASSY	 TE Part # 90035-3 DAHT PIDG FASTON 22-18 ASSY	 TE Part # 8-1377174-0 SMP 0-0165564-1	 TE Part # 169400 CERTI-LOK FRAME W/O DIES
 TE Part # 2392021-1 RED BATTERY DAHT KIT 110V (47689-4)	 TE Part # 539691-2 ERGO DIE R.B.Y	 TE Part # 169404 CERTI-LOK DIE	 TE Part # 2392021-2 RED BATTERY DAHT KIT 220V (47689-4)
 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	

Customers Also Bought





TE Part #1676979-4
TW 1W 10K 6.35X25PL




TE Part #138601-000
B-106-1401



TE Part #1-1437624-5
PKA70B1/4=KNOB PLASTIC 1/4 IN



TE Part #4-1437624-6
PKES120B1/4=KNOB PLSTC FLUTED



TE Part #2350310-1
MINI IO CONN Cat6A FI 4x2 AWG24 /26 T I



TE Part #8-2176397-6
3502 3K6 1%



TE Part #1SNA116795R1100
SCFCV1-2

TE Part #1SNA116797R1300
SCFCV4

TE Part #1SNA176791R2100
CPV4-5

TE Part #1SNA176816R1200
CPV1-2

Documents

Product Drawings

110 PIDG FASTON REC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_165564-1_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_165564-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_165564-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.