



	A	INITIAL	6NOV2015	GY	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS
SURFACE PLATING:
SILVER PLATING: $\geq 2\mu\text{m}$
GOLD PLATING: $\geq 0.75\mu\text{m}$
WIRE RANGE: $0.08\text{mm}^2\sim 0.52\text{mm}^2$ (AWG28~AWG20)
OPERATION TEMPERATURE: $-40^{\circ}\text{C}\sim +125^{\circ}\text{C}$

注释:
1. 技术参数:
公针材料: 黄铜
表面电镀:
镀银: $\geq 2\mu\text{m}$
镀金: $\geq 0.75\mu\text{m}$
接线范围: $0.08\text{mm}^2\sim 0.52\text{mm}^2$ (AWG28~AWG20)
工作温度: $-40^{\circ}\text{C}\sim +125^{\circ}\text{C}$

-	PART NUMBER AFTER PLATING				Ø d	WIRE GAUGE		STRIPPING LENGTH (mm)	
	SILVER PLATING		GOLD PLATING			MM ²	AWG		
PIN CONTACT	CAM-08	T2070001008-001	DAM-08	T2070011008-001	0.7	0.08-0.21	28-24	4.0	
	CAM-13	T2070001013-001	DAM-13	T2070011013-001	0.9	0.13-0.33	26-22		
	CAM-33	T2070001033-001	DAM-33	T2070011033-001	1.12	0.33-0.52	22-20		
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm  TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ANGLES ±- MATERIAL - - FINISH - -		DWN Gino.Yao 07AUG2015	TE Connectivity						
		CHK Chris.Wang 07AUG2015							
		APVD Xiang.Xu 07AUG2015	NAME CAM/DAM D-SUB PIN CONTACT						
		PRODUCT SPEC 108-137141							
		APPLICATION SPEC 114-137141	SIZE A3						
		WEIGHT -							
		Customer Drawing					SCALE 6:1	SHEET 1 OF 1	REV A