




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 8.36 mm²

Stud Size: M6

Stud Diameter: 6.5 mm [.256 in]

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	2.41 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	750
Packaging Method	Box

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M6
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support



Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	8.36 mm²
Stud Diameter	6.5 mm[.256 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	17 mm[.669 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 726343
SOL. RING TONGUE

Customers Also Bought



TE Part #1-5102153-3
A/L UNIV HDR 44P VERT



TE Part #788157-1
SLD CPC 13-9 PLUG,STD,SM INS




TE Part #66104-8
III+ SKT,24-20,15AU/FL,STRIP



TE Part #160533-2
110 FASTON,REC.,20-17 AWG,TPBR



TE Part #66256-4
MALE CONTACT ASSY (STRIP)





TE Part #796273-1
SLD CPC RCPT ASSY,17-14,REV SX



TE Part #1-1617037-3
HFW5A1201L00 = HFW5A RELAY



TE Part #1SNA115662R2200
M4/8.SFT



Documents

Product Drawings

SO-RINGZUNGE D46234

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_726343-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_726343-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_726343-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.