

65002-06N ✓ ACTIVE

DEUTSCH

TE Internal #: 65002-06N

Receptacle In-line Junction PCB Tail Backpack Assembly, -85 – 392 °

C [-85 – 392 °F], Terminal Junction Modules

[View on TE.com >](#)



Connectors > Terminal Junction Modules & Accessories > Terminal Junction Modules



Terminal Junction System Component Type: **Receptacle In-line Junction PCB Tail Backpack Assembly**

Compatible With Contact Size: **20**

Operating Temperature Range: **-85 – 392 °C [-85 – 392 °F]**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Body Features

Connector Seal Material	Elastomer
-------------------------	-----------

Product Type Features

Terminal Junction System Component Type	Receptacle In-line Junction PCB Tail Backpack Assembly
---	--

Contact Features

Compatible With Contact Size	20
------------------------------	----

Usage Conditions

Operating Temperature Range	-85 – 392 °C [-85 – 392 °F]
-----------------------------	-----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2024

(241)

Candidate List Declared Against: JAN 2024

(240)

SVHC > Threshold:

Pb (1.2% in Contact Lead-Copper Alloy)

Decamethylcyclopentasiloxane (D5) (5% in
Insert subassembly)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #170360-3
MINI UNIVERSAL M-N-L PIN



TE Part #CTJ122E05E-513
MODULE ASSY



TE Part #2-1617351-2
JMSP-5XM=M39016/11-018M



TE Part #52273
TERMINAL,PIDG R IR 22 4



TE Part #1-962915-3
TAB 2.8x0.8 CONTACT CS SWS Au



TE Part #2102319-2
Fortis Zd 20 Col R/A Full Shroud Assy SE



TE Part #NB09012001
ATUM-12/3-STK



TE Part #5-103168-5
14 MODII HDR DRST SHRD .100CL



TE Part #4160-204-1631L
CONT PIN



TE Part #4162-202-1631L
CONT SOC ASSY