




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 52600 – 83700 CMA

Stud Size: M8, 5/16

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Insulation Sleeve Color	Red
Stripe Color	Red

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Type Features

--	--



Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M8, 5/16
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	52600 – 83700 CMA
Stud Diameter	7.92 mm[.312 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	53.06 mm[2.089 in]
Compatible Insulation Diameter (Max)	14.22 mm[.56 in]
Compatible Insulation Diameter Range	14.22 mm[.56 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 601129-2
HAND TOOL (A.S.I.)



TE Part # 47823
HYP8/10 TERMINYL 2AWG DIE SET



TE Part # 1490406-1
HYP10 TERMINYL 2AWG DIE SET




TE Part # 1490410-1
HYP10 PLASTI-GRIP 2AWG DIE SET



TE Part # 48755-1
HYP8 PLASTI-GRIP 2AWG 69051 DIE SET


Also in the Series | PLASTI-GRIP



Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)



Spade Terminals(159)



Splices(45)


Customers Also Bought



TE Part #CV7362-000
202K142-25L-0



TE Part #1-171196-0
6 POS MATE-N-LOK S



TE Part #1-284391-2
TERMI-BLOK PCB SIDE ENTRY STAC



TE Part #1-1437597-7
2SWK131AL101=NON UL KEYLOCK SW



TE Part #5-146282-3
03 MODII HDR SRST B/A .100CL



TE Part #2176246-7
CRGS2512 5% 3R3




TE Part #53407-1
PIDG PVF2 R 22-16COM22-18MIL 6



TE Part #8153950001
D-SCE-18-50-4



TE Part #52044-2
TERMINAL R PG 2 3/8



TE Part #JN1003A08-98SA-1
RECEPT.JAM NUT #8(HDJ)

Documents

Product Drawings
TERMINAL R PG 2 5/16
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_52044-4_L2d_dxf.zip



English

Customer View Model
[ENG_CVM_CVM_52044-4_L.3d_igs.zip](#)

English

Customer View Model
[ENG_CVM_CVM_52044-4_L.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model
[ENG_CVM_52044-4_J.2d_dxf.zip](#)

English

Customer View Model
[ENG_CVM_52044-4_J.3d_igs.zip](#)

English

Customer View Model
[ENG_CVM_52044-4_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
[Application Specification](#)

English

Instruction Sheets
[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals
[UL Report](#)

English

[UL Report](#)

English