



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
Primary Product Color: **Black**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features



Housing Material	Nylon
Centerline (Pitch)	12 mm[.472 in]

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 1-1743206-2
250 FLAG P-LOCK HSG 2P 12.0 BLK GWT



TE Part # 1-1743165-1
PL EX 2P .250 (6.3 MM) FLAG NATURAL




TE Part # 1743165-8
250 HSG. PL EX FLAG REC. 12mm 2P BLUE




TE Part # 1743206-2
POSITIVE LOCK 250 RECEPTACLE




TE Part # 1743165-1
POSITIVE LOCK 250 RECEPTACLE



TE Part # 1-1743165-8
PL EX 2P .250 (6.3 MM) FLAG BLUE



TE Part # 1-1743165-5
250 HSG. PL EX REC. 12mm 2P YELLOW



TE Part # 1743165-5
POSITIVE LOCK 250 RECEPTACLE



TE Part # 1-1743165-2
250 HSG. PL EX REC. 12mm 2P BLACK




TE Part # 1743206-1
POSITIVE LOCK 250 RECEPTACLE

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(184)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(4)



Quick Disconnects(185)

Customers Also Bought



TE Part #917693-1
2.5 SIGNAL D/LOCK PLUG HSG 9P



TE Part #CAT-SI261-T669
Signal Double Lock TPA



TE Part #917765-1
2.5 SIGNAL D/LOCK TAB CONT. M



TE Part #917701-1
2.5 SIGNAL DBL LOCK DLP 5P



TE Part #1744544-7
EP II TPA 07P, BLACK




TE Part #1-1743165-5
250 HSG. PL EX REC. 12mm 2P YELLOW



TE Part #5-368572-2
FOAMING PROOF CAP 3POS RED



TE Part #2299293-2
POD-LOK 187 FLAG RCPT.AWG 20-16 PTPBR



TE Part #4-1903414-2
GHC 9.0 3POS PLUG HSG BLACK

Documents

Product Drawings

250 HSG. PL EX REC. 12mm 2P BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1743165-2_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1743165-2_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1743165-2_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English

Agency Approvals

UL Report

English