




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
PCB Thickness (Recommended): **3.63 – 4.45 mm [.143 – .175 in]**
Mating Tab Width: **4.75 mm [.187 in]**
Mating Tab Thickness: **.51 mm [.02 in]**
PCB Hole Diameter: **1.4 mm [.055 in]**

Features

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	10000
Packaging Method	Box

Dimensions

Extension Below Board	5.2 mm[.204 in]
PCB Thickness (Recommended)	3.63 – 4.45 mm[.143 – .175 in]
PCB Hole Diameter	1.4 mm[.055 in]
Profile Height from PCB	7.8 mm[.311 in]

Contact Features

PCB Contact Termination Area Plating Material Thickness	4.5 µm[177.16 µin]
Contact Underplating Material Thickness	2.5 µm[98.42 µin]
Contact Mating Area Plating Material Thickness	4.5 µm[177.16 µin]



PCB Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Terminal Size	4.75
Terminal Orientation	Right Angle

Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Printed Circuit Board

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1-726389-2
187 FASTON,FLAG,TAB,TPBR

TE Part # 61907-1
187 FASTON TAB TPBR

TE Part # 170001-2
187 FASTON,TAB,TPBR

TE Part # 726388-2
187 FASTON TAB TPBR

TE Part # 1-726388-2
187 FASTON,TAB,TPBR

TE Part # 1-726386-2
250 FASTON,TAB,TPBR

TE Part # 170001-3
187 FASTON,TAB,TPBR

TE Part # 61914-1
187 FASTON TAB PBR

TE Part # 61951-1
187 FASTON TAB TPBR

Also in the Series | FASTON 187

Crimp Terminal Housings(41)

Insertion & Extraction Tools(1)

Joints & Splices(1)

PCB Terminals(42)



[Quick Disconnects\(207\)](#)



[Splices\(1\)](#)


Customers Also Bought



TE Part #4-2176058-1
[RLP73K 3A R47 5% 2K RL](#)



TE Part #6-2176459-1
[SMW 7W 33R 5% Taped](#)




TE Part #61137-1
[.093 PCB PIN .0126 PTP PH/BZ](#)



TE Part #ANT-LTE-SP610-T
[Antenna SP610 PCB RPC LTE SMT T&R](#)




TE Part #5-2176349-6
[CRGCQ 2512 390K 1%](#)




TE Part #4-2176381-5
[RQ 0805 35K7 0.1% 10PPM 5K RL](#)




TE Part #827001-2
[4P MNL STIFTSOCKEL](#)



TE Part #2-2176562-8
[3430 H2 1% 12R 100ppm 1k RL](#)



TE Part #104113-E
[ERMB 125 FS 1 EE * 3,70 A-E V-V * 247](#)



TE Part #104114-E
[ERMC 55 FS 1 EE * 3,70 A-E V-V * TRAY 24](#)

Documents

Product Drawings

[187 FASTON TAB TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_726389-2_F.2d_dxf.zip](#)

726389-2

Tab, 4.75 mm [.187 in] Tab Width, PCB Hole Diameter 1.4 mm [.055 in], Through Hole
- Solder, Tin Plating, Box, FASTON 187, PCB Terminals



English

Customer View Model

[ENG_CVM_CVM_726389-2_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_726389-2_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.