




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2.08 – 5.26 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	19.56 mm[.777 in]
Compatible Insulation Diameter Range	3.81 – 5.08 mm[.15 – .2 in]
Terminal Material Thickness	.46 mm[.018 in]
Wire Size	2.08 – 5.26 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-160521-2
375 FASTON REC 12-10 AWG TPBR

TE Part # 2150237-2
OCEAN_2.0_APPLICATOR-E-130F210O-REA

TE Part # 171706-1
FASTON 250 INS POD NYLON NAT

TE Part # 2376579-2
250 FASTON PCB TAB TPBR

TE Part # 2-171706-1
FASTON 250 INS POD NYLON NAT

TE Part # 58525-2
PROCrimper DIE

TE Part # 2376595-2
250 FASTON PCB TAB TPBR

TE Part # 2150237-1
OCEAN_2.0_APPLICATOR-E-130F210O-REM

TE Part # 90120
DAHT 250 FASTON REC 14-10 ASSY

TE Part # 2376591-2
250 FASTON PCB TAB TPBR

TE Part # 2376582-2
250 FASTON PCB TAB TPBR

TE Part # 7-2150237-7
OCEAN_2.0_SPARE_PART_KIT-130F210O

Also in the Series | FASTON 250



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(425)



Splices(4)


Customers Also Bought




TE Part #4-2176094-0
RP 2A 0.25W 309K 0.1% 25PPM 1K RL



TE Part #41771-1
250 FASTON REC 22-18 AWG BR




TE Part #2-1623783-1
SQM7 100K 5% (METAL FILM)




TE Part #521998-2
ULTRA-POD 250 ASSY REC 18-14 AWG TPBR




TE Part #3-336369-5
250 FASTON HSG.,REC.,1 POS,BLACK




TE Part #350189-1
.058 DIA RECPT PC R/A LP 26-22




TE Part #1734839-6
FPC CONN. 0.5MM PITCH T/C, 6P



TE Part #2196262-1
ARM LEVER BLACK MOULDED



TE Part #2196263-1
HOUSING BODY



TE Part #2196264-1
FIXED PLUG

Documents



Product Drawings

250 FASTON REC 14-10 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_41450-1_DD.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_41450-1_DD.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_41450-1_DD.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English