



EMI & EMC Solutions > EMI Filters > Power Entry Modules > CORCOM P SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**

Input Voltage Selection: **Single AC**

Filter Switch Type: **DPST**

Filter Shield Type: **Filter Shield**

Product Orientation: **Vertical**

[All CORCOM P SERIES MULTI-FUNCTION INLET FIL \(261\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Snap-In
--------------------------	---------

Dimensions

Panel Thickness (Recommended)	.13 – 1 mm
-------------------------------	------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Configuration Features

Extender Options	None
Fuse Options	Dual

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	DPST



Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Input Voltage Selection	Single AC
Leakage Current (Max) (120VAC, 60Hz)	250 µA
Leakage Current (Max) (250VAC, 50Hz)	500 µA
Current Rating	3 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	Filter Shield
Product Orientation	Vertical

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1609140-3
PA105 J0=F6806



TE Part # 1609140-1
PA100=F6800




TE Part # 1609146-2
PA102 CONNECTOR PIN=F6999




TE Part # 1609146-1
PA101 CONNECTOR PLU=F6998

Also in the Series | Corcom P




EMI & EMC Accessories(4)




Power Entry Modules(317)


Customers Also Bought



TE Part #CAT-P592-L853
PIDG Long Spring Spade Tongue Terminals



TE Part #820182-000
381A301-71-0




TE Part #GA10K3A11B
DISCRETE 10K OHMS,+/-0.2C FROM 0C TO 70C



TE Part #5745171-2
SIZE 1 ASSY KIT .200




TE Part #1052422-1
2052 0000 02,SMA FM JACK RECPT



TE Part #991496-000
QFT2-130/42-0



TE Part #861647-8
RECPT FLANGED HV 7 CONTACT



TE Part #863024-1
LGH PLUG ASSY HV 7 PIN



TE Part #A1004RT24K1-F
NTC THERMISTOR ASSEMBLY

Documents

Product Drawings

PS0S0DS3A=C1182

English

CAD Files

Customer View Model

ENG_CVM_7-6609107-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_7-6609107-0_A.3d_stp.zip

English

Customer View Model

ENG_CVM_7-6609107-0_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-6609107-0_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-6609107-0_O.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_7-6609107-0_O.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

PS0S0DS3A

Power Entry Module, Single AC Input, DPST, Filter Shield, Vertical, 3 A, .187"
FASTON Output, 250 VAC, Filtered, Corcom P, Power Entry Modules

