




Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Hood & Base Locking Device Type: **Locking Clip**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Mechanical Attachment

Thread Size	AG
Hood & Base Locking Device Type	Locking Clip

Product Type Features

Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # T1210320125-000
[H32B-TS-M25](#)



TE Part # T1220320125-000
[H32B-TG-M25](#)











TE Part # T1200320240-000
[H32B-TG/S-2M40](#)



TE Part # T1220320148-000
[H32B-TG-PG48](#)




 TE Part # T2100323201-000 HEAV-016-FS 17-32	 TE Part # T1210320140-000 H32B-TS-M40	 TE Part # T2020802201-000 HD-040-F 41-80	 TE Part # T1000321320-000 H32B-KDBP-BOM
 TE Part # T2040324201-000 HE-016-FC 17-32	 TE Part # CAT-H3399-IN722A HDC HEEE Insert Series, Rail Compliant	 TE Part # T2040323201-000 HE-016-FS 17-32	 TE Part # T1000321220-000 H32B-KDBP-BOM-NA
 TE Part # T1210320129-000 H32B-TS-PG29	 TE Part # T1320320150-000 H32B-TG-RO-M50	 TE Part # T1210320136-000 H32B-TS-PG36	 TE Part # T1210320120-000 H32B-TS-M20
 TE Part # T1220320325-000 H32B-TG-3M25	 TE Part # T2050962201-000 HEEE-048-F 49-96	 TE Part # T2040322201-000 HE-016-F 17-32	 TE Part # T2031442201-000 HDD-072-F 73-144

Also in the Series | [HDC IP65](#)



Rectangular Connector Hoods & Bases
(1257)

Customers Also Bought



TE Part #T1210320129-000
H32B-TS-PG29



TE Part #T1220160121-000
H16B-TG-PG21



TE Part #T2040162101-000
HE-016-M



TE Part #T2040162201-000
HE-016-F



TE Part #T1410162000-000
H16B-AG



TE Part #T1410242000-000
H24B-AG



TE Part #T2030722201-000
HDD-072-F



TE Part #T2031082201-000
HDD-108-F



TE Part #T2031442201-000
HDD-072-F 73-144



TE Part #T1230160129-000
H16B-TSH-PG29

Documents

Product Drawings

H32B-AG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1410322000-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1410322000-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1410322000-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English