




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 3

Terminal Block Connector Type: **Receptacle**

Connector System: **Wire-to-Board**

Centerline (Pitch): **2.54 mm [.1 in]**

Number of Rows: 1

Features

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Method to Wire & Cable	Push-in
Termination Post & Tail Length	3.5 mm

Body Features

Primary Product Color	Green
Product Orientation	Vertical

Packaging Features

Packaging Method	Box
------------------	-----

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper
Contact Current Rating (Max)	6 A

Housing Features

--	--



Housing Material	High Temperature Polyamide
Centerline (Pitch)	2.54 mm[.1 in]

Configuration Features

Wire Entry Location	Side
Stacking Configuration	Side Stackable
Number of Positions	3
Number of Rows	1
Wire Entry Angle	90°

Product Type Features

Terminal Block Connector Type	Receptacle
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Electrical Characteristics

Operating Voltage	150 VAC
-------------------	---------

Dimensions

Wire Size	26 – 20 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)



	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2834006-1
RELEASE POKE-IN
CONNECTOR_1POLES



TE Part # 2834385-2
RELEASE POKE-IN
CONNECTOR_2P_NATURAL



TE Part # 2834334-2
4.0PITCH ITB CONN_2P_W
CAP_NATURAL



TE Part # CAT-SL36-M6642B
Miniature Headers, SlimSeal

Customers Also Bought



TE Part #1924487-3
MOUNTING CLIP, AMPSEAL 16



TE Part #776495-3
AS16,CAP ASSY,ST,08P,N SEAL,CODE
C



TE Part #2-1393122-8
KHAU-17A12-120=KH



TE Part #2350514-3
3POS TB HDR 90 DEG, PITCH 3.5 & TL
3.5mm



TE Part #2176343-4
CRGCQ 1206 18R 1%

TE Part #796635-4
4 POS 5.08MM R/A PLUG,TRM BLK

TE Part #9-1879663-9
H8 1K13 0.1% 15PPM

TE Part #1-6609028-5
10VK7=F7145 S0

TE Part #D41432-000
WP-318064-10-9

TE Part #T4161420008-001
RPC-M12-FR-8CON-PUR-0.5SH

Documents

Product Drawings

3POS 2.54MM SES CONN.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2834016-3_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2834016-3_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2834016-3_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Modular Screwless Terminal Blocks Flyer

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

1-2834016-3

3 Position PCB Terminal Block, Receptacle, Wire-to-Board, 2.54 mm [.1 in] Centerline,
1 Row, 90° Wire Entry Angle, 26 – 20 AWG, .14 – .5 mm² Wire



English