



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Dimensions

Product Length	23.1 mm[.91 in]
----------------	-----------------

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
---------------	------------



Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	7.7 mm[.303 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 280543-5 FF 250 REC HSG 2P NYLON BLACK	 TE Part # 170258-2 FF 250 REC 14-12AWG TPBR REREELING	 TE Part # 1534690-1 FASTIN FASTON HOUSING 4POS 2,8 MM	 TE Part # 880137-2 3W FASTIN-ON REC. HSG
 TE Part # 170258-1 FF 250 REC 14-12AWG BR REREELING	 TE Part # 521381-1 FF 187 REC HSG 6P NYLON BLACK	 TE Part # 880097-1 2 WAY FASTIN ON HSG	 TE Part # 480100-1 FF 312 REC HSG 3P NYLON BLACK
 TE Part # 880107-2 HOUSING 8P .110 FASTON	 TE Part # 281993-3 FF 250 & 375 REC HSG 2P NYLON BLACK	 TE Part # 626213-2 3 CIR FASTIN-ON RECP HSG PRETO BLACK	

Also in the Series | FASTIN-FASTON 250

 Crimp Terminal Housings(207)	 Insertion & Extraction Tools(2)	 PCB Terminals(2)	 Quick Disconnects(250)
---	--	---	---

Customers Also Bought






TE Part #CAT-P592-SP118
PIDG Spade Tongue Terminals



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #350390-1
.140 DIA SOK 14-10 PTPBR L/P




TE Part #150530-1
FASTON 375 AM REC 2-6MM2 0.2X1.062 BR



TE Part #66597-1
III+ PIN,18-14,TIN-LEAD,STRIP



TE Part #035377P003
ES1000-NO.3-B8-X-75MM



TE Part #2-1586038-2
22P VRT HDR VAL-U-LOK V0



TE Part #350639-1
MNL PIN PTPBR

Documents

Product Drawings
FF 250 REC HSG 2P NYLON BLACK
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_480115-3_AR.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_480115-3_AR.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_480115-3_AR.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages
FASTIN_FASTON_Product_Line
English
White Paper: Nylon Discoloration
English

Product Specifications
Application Specification
English

480115-3

Receptacle, Receptacle, 2 Position, Straight, UL 94V-2, Black, Nylon, Cable Mount
(Free-Hanging), Carton, FASTIN-FASTON 250, Crimp Terminal Housings

