

Passive Components &gt; Resistors &gt; Surface Mount Resistors

Resistor Type: **Current Sensing Resistor**Element Type: **Thick Film**Package Size Code: **0508**Power Rating: **1 W**Resistance Value: **.27  $\Omega$** 

## Features

### Usage Conditions

Operating Temperature Range **-55 – 155  $^{\circ}$ C**Temperature Coefficient  **$\pm 200$  ppm/ $^{\circ}$ C**

### Product Type Features

Resistor Type **Current Sensing Resistor**Element Type **Thick Film**Package Size Code **0508**

### Configuration Features

Number of Resistors **1**

### Electrical Characteristics

Power Rating **1 W**Resistance Value **.27  $\Omega$** Resistance Class **Up to 1k $\Omega$** Passive Component Tolerance **1 %**

### Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

### Dimensions

Product Height	.6 mm [.024 in]
Product Length	1.25 mm [.049 in]
Product Width	2 mm [.079 in]

### Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-2176538-8  
RLW73P A2 1% R27 200ppm 1k RL

## Also in the Series | CGS RLW73



Surface Mount Resistors(352)

## Customers Also Bought



TE Part #1571983-4  
GDH04S04=DIP SWITCH



TE Part #2-1879494-5  
CRGH0603 5% 10R 0.2W



TE Part #L9000053-01  
Antenna 2.4 FPC SH 12x8 100 MHF4



TE Part #2342838-2  
AVP16M H. FLAT AIB NL 500MM/2X3



TE Part #CONSMA007-R178  
SMA Plug 50 Ohm Cable Crimp



TE Part #2-2176339-0  
CRGCQ 0603 390R 1%



TE Part #216264-000  
55A0111-26-3



TE Part #CAT-HST-RW175  
RW-175 Heat Shrink Tubing



## Documents

### Product Drawings

[RLW73P A2 1% R27 200ppm 5k RL](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2176537-8\\_BA.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2176537-8\\_BA.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2176537-8\\_BA.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[CGS Wide Terminal Current Sense Resistor RLW73](#)

English

[Wide Terminal Current Sense Resistor - Type RLW73 Series](#)

English