




EMI & EMC Solutions > EMI Filters > Power Entry Modules > CORCOM P SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry (Filtered/Unfiltered)**
Input Voltage Selection: **Dual AC (Series/Parallel)**
Filter Switch Type: **DPST**
Filter Shield Type: **Complete Shield**
Product Orientation: **Vertical**

[All Corcom P Series Multi-Function Inlet Fil \(261\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Dimensions

Panel Thickness (Recommended)	.79 – 2 mm[.031 – .079 in]
-------------------------------	----------------------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Configuration Features

Extender Options	None
Fuse Options	Dual

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry (Filtered/Unfiltered)



Filter Switch Type	DPST
Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Electrical Characteristics

Input Voltage Selection	Dual AC (Series/Parallel)
Leakage Current (Max) (120VAC, 60Hz)	2 µA
Leakage Current (Max) (250VAC, 50Hz)	5 µA
Current Rating	10 A
Operating Voltage	115 VAC, 230 VAC

Body Features

Filter Shield Type	Complete Shield
Product Orientation	Vertical

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1609140-3
PA105 J0=F6806



TE Part # 1609140-1
PA100=F6800




TE Part # 1609146-2
PA102 CONNECTOR PIN=F6999




TE Part # 1609146-1
PA101 CONNECTOR PLU=F6998

Also in the Series | Corcom P



EMI & EMC Accessories(4)



Power Entry Modules(317)

Customers Also Bought



TE Part #1-338313-2
9POS.HD-20 REC.ASSY



TE Part #3-640440-3
03P MTA100 CONN ASSY 22AWG RED



TE Part #640456-3
03P MTA100 HDR ASSY F/L SQ STR



TE Part #3-643817-5
05P MTA156 CONN ASSY 18AWG ORA




TE Part #3-640428-3
03P MTA156 CONN ASSY 22AWG RED



TE Part #640388-3
03P MTA156 HDR ASSY RN STR F/L



TE Part #640445-3
03P MTA156 HDR ASSY FL/STR SN



TE Part #643067-3
03P MTA156 MOLDED COVER



TE Part #1-66105-6
III+ SKT,24-20,TIN-LEAD,SMPACK



TE Part #2-2176340-7
CRGCQ 0603 22K 5%

Documents

Product Drawings

PM0SXDSXB=C3346

English

CAD Files

Customer View Model

ENG_CVM_3-6609940-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_3-6609940-2_A.3d_stp.zip

English

Customer View Model

ENG_CVM_3-6609940-2_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-6609940-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-6609940-2_O.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_3-6609940-2_O.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

