



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.65 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Locking Lance Height	1.2 mm[.05 in]
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Other

Line	FASTON .250
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	500
--------------------	-----



Packaging Method

Loose Piece/Carton

Dimensions

Product Length	19.2 mm[.755 in]
Compatible Insulation Diameter Range	2.31 – 3.3 mm[.091 – .13 in]
Terminal Material Thickness	.33 mm[.013 in]
Wire Size	.51 – 1.65 mm²

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 539653-2
MATRIZE .250 FF

TE Part # 1-1579007-4
EXTRACTION TOOL

TE Part # 4-1579007-3
EXTRACTION TOOL KIT

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(207)

Insertion & Extraction Tools(2)

PCB Terminals(2)

Quick Disconnects(250)

Customers Also Bought

TE Part #213860-1
23-37 RCPT HSG,STD SEX,CPC

TE Part #213866-1
23-24 RCPT HSG,STD SEX,CPC

TE Part #925612-1
STC REC 6.3 Contact SRC Sn

TE Part #ZPF000000000019068
FDBA 56-10-6 PN-K



TE Part #ZPF000000000019114
FDBA 56-12-10 PN-K

TE Part #928934-2
FF 250 TAB 20-17 AWG .015 TPBR

TE Part #ZPF000000000018082
FDBA 50-14-12 SN-K

TE Part #ZPF000000000018455
FDBA 50-22-21 SN-K

TE Part #ZPF000000000018581
FDBA 50-24-31 SN-K 090

TE Part #926298-1
4P UNIV.M-N-L.CAP

Documents

Product Drawings

FF 250 REC 0.5-1.5MM2 TPPB LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_925603-2_AN.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_925603-2_AN.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_925603-2_AN.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.