



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**
Element Type: **Thin Metal Film**
Package Size Code: **1206**
Power Rating: **.125 W**
Resistance Value: **4.87K Ω**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±25 ppm/°C

Electrical Characteristics

Operating Voltage	150 V
Power Rating	.125 W
Resistance Value	4.87K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Metal Film
Package Size Code	1206



Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.05 mm[.12 in]
Product Width	1.55 mm[.061 in]

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-1614968-4 CPF 1206 2K49 0.1% 25PPM 5K RL	 TE Part # 1614968-3 CPF1206 20K 0.1% 25PPM 5K RL	 TE Part # 8-1614968-1 CPF 1206 10K2 0.1% 25PPM 5K RL	 TE Part # 6-1614968-2 CPF 1206 6K04 0.1% 25PPM 5K RL
 TE Part # 5-1614968-0 CPF1206 2K49 0.1% 25PPM 1K RL	 TE Part # 5-1614968-4 CPF 1206 4K99 0.1% 25PPM 5K RL	 TE Part # 7-1614968-4 CPF 1206 8K25 0.1% 25PPM 5K RL	 TE Part # 1614968-2 CPF1206 21K5 0.1% 25PPM 5K RL

Also in the Series | Neohm CPF

Surface Mount Resistors(5842)

Customers Also Bought

 TE Part #9-1625971-5 HSA25 R01 10%	 TE Part #2337238-3 TACT MINI GW 5.2X5.2X2 160GF	 TE Part #3-2176307-2 RP 1E 0.1W 26K1 0.1% 25PPM 5K RL	 TE Part #7-2176305-3 RP 1E 0.1W 604R 0.1% 25PPM 5K RL
---	--	--	--

CPF1206B4K87E

Surface Mount Precision Resistor, Thin Metal Film, 1206, .125 W, 4.87K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Neohm CPF






TE Part #1-1879353-9
[RR02 5% 24K AMMO](#)




TE Part #7-1879354-5
[RR03 5% 390R AMMO](#)




TE Part #7-1879648-1
[H4P 287R 0.5% 100PPM](#)



TE Part #1-830611-0
[LGH 1/2 SNGL MLD END](#)



TE Part #3-1437162-8
[FSP-12A-11](#)



TE Part #2-2176392-9
[RQ 1206 261K 0.1% 10PPM 5K RL](#)

Documents

Product Drawings

[CPF 1206 4K87 0.1% 25PPM 5K RL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5-1614968-3_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1614968-3_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1614968-3_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CPF-1016](#)

English