



Connectors > Automotive Connectors > Automotive Housings > Circular DIN Housings



Number of Positions: 7

Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: **1.5 mm [.059 in]**

Connector System: **Wire-to-Wire**

Sealable: **Yes**

[All Circular DIN Housings \(64\)](#)

Features

Housing Features

Housing Material	PBT GF30
------------------	----------

Industry Standards

IP Rating	IP69K
UL Flammability Rating	UL 94HB

Dimensions

Product Length	31 mm[1.22 in]
Connector Height	32.8 mm[1.291 in]

Packaging Features

Packaging Method	Box
Packaging Quantity	500

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No



Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Other

Serviceable	No
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	48 VDC
Nominal Voltage Architecture	24 V, 42 V, 12 V, 48 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Blue
Connector & Keying Code	A

Contact Features

Contact Size	1.5mm
Contact Type	Socket
Mating Pin Diameter	1.5 mm[.059 in]

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	7
---------------------	---

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]



Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 185636-1
PROTECT CAP 2.5MM PLUG



TE Part # 1-1718230-1
1,5MM PIN HSG 5-7 POS ASSY



TE Part # 828904-1
SINGLE WIRE SEAL FOR J.P.T.CON



TE Part # 828922-1
2,5MM CAVITY PLUG FOR 5,4MM DI



TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET




TE Part # CAT-C4962-B128
Circular DIN Backshells




TE Part # 185792-1
180 DEG CAP FOR CORRUGTD TUBE

Customers Also Bought




TE Part #2029111-3
3P PLUG SR VAL-U-LOK FH GW



TE Part #342183-1
12-10 F.E.P.G. RING TONGUE 3BA




TE Part #1-770166-0
02P MINI-UMNL ASSY VO SNNI*



TE Part #1586765-6
6P RCPT VAL-U-LOK GW




TE Part #8-34145-1
PG R 22-16 COMM 22-18 MIL 8



TE Part #1586862-6
6P FH PLUG VAL-U-LOK FH GW



TE Part #1-1969688-5
PTL 1X5 PCB HEADER VERT HITEMP KEY A LGR



TE Part #120957-1
UPM EXPANDED PIN ASSEMBLY KEY A LGR



TE Part #4-794677-6
16POS MICRO MNL ASSY,R/A,THRU



TE Part #2329592-2
20POS,MQS,REC HSG,UNSLD

Documents

Product Drawings
1,5MM BU-STE,BL 7P
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-967650-1_G_c-1-967650-1-g.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-967650-1_G_c-1-967650-1-g.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-967650-1_G_c-1-967650-1-g.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English