




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **5.21 mm [.205 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	20000
Packaging Method	Strip/Reel

Dimensions

Product Length	15.64 mm[.616 in]
Compatible Insulation Diameter Range	2.16 – 3.18 mm[.085 – .125 in]
Terminal Material Thickness	.33 mm[.013 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	5.21 mm[.205 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




KIT

TE Part # 7-2150258-7
[OCEAN_2.0_SPARE_PART_KIT-090F140F](#)




TE Part # 2150258-2
[OCEAN_2.0_Applicator-E-090F140F-REA](#)



TE Part # 2150258-1
[OCEAN_2.0_Applicator-E-090F140F-REM](#)




TE Part # 42197-2
[205 FASTON REC 22-18 AWG TPBR](#)



TE Part # 60674-1
[205 FASTON REC 26-22 AWG TPBR](#)

Also in the Series | **FASTON 205**



[Crimp Terminal Housings\(3\)](#)



[PCB Terminals\(10\)](#)



[Quick Disconnects\(35\)](#)

Customers Also Bought



TE Part #52935-1
TERMINAL,PIDG SPR SPD 16-14 6



TE Part #36922
TERMINAL,SOLIS R 2/0 5/16



TE Part #60415-1
110 FASTON REC 22-18 AWG TPBR



TE Part #8-2176370-8
RQ 0603 3K48 0.1% 10PPM 5K RL




TE Part #M3051-000005-05KPG
PRESS XDCR M3051-000005-05KPG



TE Part #321874
TERMINAL,SOLIS R 3/0 5/16




TE Part #36919
TERMINAL SOLIS RING 1/0 1/2



TE Part #172777-1
MIC MARE-2 TAB CONTACT



TE Part #117366-000
T200-RIBBON-WH



TE Part #172775-1
MIC MK-2 REC B TYPE

Documents

Product Drawings

205 FASTON REC 22-18 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42198-2_BE.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42198-2_BE.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42198-2_BE.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



FASTON Tabs

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English