




EMI & EMC Solutions > EMI Filters > Modular Jack Filters



EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Product Type Features

Output Termination Type	PCB Mount
Filtering Requirements	Filtered
Filter Connector Type	8-Pin Jack, RJ45 Connector

Configuration Features

Number of Loaded Positions	8
----------------------------	---

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-406541-1
MJ,INV,1X1,6PNL G.,100"ST,SN



TE Part # 1987236-1
RJ45 CONNECTOR IP20 45 DEG., INDUSTRIAL

Also in the Series | Ethernet Magnetics



Modular Jack Filters(30)

Customers Also Bought



TE Part #5227161-1
RTANG JK W/MTG PINS, BNC PCB

TE Part #2-323914-2
TERMINAL,PIDG R IR 24 4

TE Part #413990-1
STR JACK, SMB, PCB

TE Part #2081156-1
SMA Jack S/T RF CONN, PIP

TE Part #5745122-2
STR REL ASSY 15 POS SZ 2 AMPLI

TE Part #474319-000
202A132-25/86-0

TE Part #2311763-3
AMPL REC, HD22, R/A, 15P, THREADED

TE Part #2337822-2
DISCR.ETH.MAG. 1GB SINGLE SMT

TE Part #2383942-8
TERMI-BLOK SMD MOUNT 180_8P_3. 5 MM

TE Part #1478885-2
PG EMC GLAND PG9

Documents

Product Drawings

DISCR.ETH.MAG. 10/100 SINGLE SMT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2337822-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2337822-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2337822-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DISCRETE MAGNETICS FOR INDUSTRIAL ETHERNET

English

Product Specifications

Application Specification

English