


Cable Assemblies > Data Bus Components > Data Bus Terminators



Data Bus Connector Type: **Plug**

Data Bus Connector Style: **Bayonet**

Polarization Code: **A**

Contact Type: **Socket**

Impedance: **3000 Ω**

Features

Usage Conditions

Operating Temperature (Max)	125 °C
-----------------------------	--------

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Product Type Features

Data Bus Connector Type	Plug
-------------------------	------

Data Bus Connector Style	Bayonet
--------------------------	---------

Mechanical Attachment

Polarization Code	A
-------------------	---

Contact Features

Contact Type	Socket
--------------	--------

Electrical Characteristics

Impedance	3000 Ω
-----------	--------

Other

EU RoHS Compliance	Not Compliant
--------------------	---------------

EU ELV Compliance	Not Compliant
-------------------	---------------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (37% in Solder) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 750984-004
10612-24-9

Customers Also Bought

TE Part #696684-000
B-051-01-01TE Part #69692-1
T-HEAD PIDG STRATO 26-20 ASSYTE Part #ZPF000000000012475
DBAS 70-19-0 PNTE Part #ZPF0000000000206936
DBAS 70-19-0 SN 395TE Part #ZPF000000000012621
DBAS 70-37-0 SN 395TE Part #ZPF0000000000206933
DBAS 70-61-0 SN 395TE Part #ZPF0000000000137966
DBAS 78-12-0 SN 059TE Part #ZPF000000000013798
DBAS 78-19-0 SN 059TE Part #ZPF0000000000206937
DBAS 78-37-0 SN B5974TE Part #AAG4888-00
BCH1-17-1-B-L50-WR5-02

Documents

Product Drawings

[D-621-0473-L](#)

English

Datasheets & Catalog Pages

[Data Bus Components Brochure](#)

English

Product Specifications

[Product Specification](#)

English

[Product Specification](#)

English