




EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters > 3 Phase Filters, Corcom BCF Series



Current Rating: 42 A

Input Termination Type: Terminal Block

Output Termination Type: Terminal Block

Wiring Configuration: DELTA (3 wire + ground)

Operating Voltage: 480 VAC

[All 3 Phase Filters, Corcom BCF Series \(0\)](#)

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Terminal Block
Output Termination Type	Terminal Block

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	6.9
Current Rating	42 A
Operating Voltage	480 VAC

Configuration Features

Wiring Configuration	DELTA (3 wire + ground)
----------------------	-------------------------

Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance	Compliant with Exemptions
-------------------	---------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series |

Customers Also Bought




TE Part #167501-2
FEMALE SCREWLOCK



TE Part #1241050-4
2x4P MOD II BREAK AWAY HDR,SMD,
BLISTER



TE Part #5-103414-1
03 MODII HDR SRST SHRD LF



TE Part #154718-3
PL 250 REC 0.7-2.0 MM2 0.406 TPBR



TE Part #1676142-3
RN 0805 100K 0.1% 10PPM 5KRL



TE Part #1969608-5
5P VAL-U-LOK TPA 22-18 AWG




TE Part #5-104178-5
08 SYS 50 HDR SRST UNSHRD SN



TE Part #4-1625867-4
RP 1J 0.166W 17R4 0.1% 25PPM 1K RL



TE Part #8-1614353-4
RN 0603 47K5 0.1% 10PPM CUT
LENGTH



TE Part #1-1969598-0
10P FH PLUG VAL-U-LOK V2

Documents

Product Drawings

42BCF10R=F8235E

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1609989-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1609989-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1609989-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Corcom BCFxR Flyer
English