




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Cavity Plug**

Primary Product Material: **Silicone Rubber**

Primary Product Color: **Black**

Shore A Hardness: **50**

Operating Temperature (Max): **140 °C [284 °F]**

Features

Packaging Features

Packaging Method	Carton
Packaging Quantity	5000

Product Type Features

Connector Seal & Plug Type	Cavity Plug
----------------------------	-------------

Body Features

Primary Product Material	Silicone Rubber
Primary Product Color	Black

Other

Shore A Hardness	50
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Usage Conditions

Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold









EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 953756-1 47W RCPT HSG ASSY	 TE Part # 1379208-3 26W ASSY RECEPTACLE HSG	 TE Part # 1379208-4 26W ASSY RECEPTACLE HSG	 TE Part # 953756-9 47W RCPT HSG ASSY
 TE Part # 1-1379208-1 26W ASSY RECEPTACLE HSG	 TE Part # 953756-7 47W RCPT HSG ASSY	 TE Part # CAT-T4827-CH8172 Timer Connector Housing	

Customers Also Bought






TE Part #T4162114005-002
RPC-M12-5MS-1.0SH-M12-5FR-PVC



TE Part #2310923-1
2P 8MM HV,PLUG HSG,ASSY,SEALED, V0,A



TE Part #1394353-2
FLACHSTE A-P 1,5



TE Part #1544627-3
POWER RECPT CONT, 6.3 TO 9.5 MM, SOLDER



TE Part #2188250-2
JPT 4P SLD PLUG ASS'Y



TE Part #2208669-3
8MM HV, CONTACT,ASSY



TE Part #544720-E
SRCBUG A 2,54 2 2 CSI 163 * K-AD B500 J



TE Part #1394909-2
SHIELD, 180 DEG., 94POSN. RECEPTACLE HSG



TE Part #2399908-1
TYPE 1,CHARGE INLET HSG,DUST CAP



TE Part #2400717-1
GB/T DC,CHARGE INLET BRACKET

Documents

Product Drawings

CAVITY PLUG

English

CAD Files

Customer View Model

ENG_CVM_100132-1_A3.3d_igs.zip

English

Customer View Model

ENG_CVM_100132-1_A3.3d_stp.zip

English

Customer View Model

ENG_CVM_100132-1_A3.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

French

Instruction Sheets

Instruction Sheet (non U.S.)

French