

AKUA013NN00410240000

✓ ACTIVE

TE Internal #: AKA013N00410240000
Cable-to-Cable, Signal, Cable Mount (Free-Hanging),
Electrodeposited Nickel, Zinc Alloy, PBT, Shell Size 23, Shielded, 0°
Alignment Keyed, Metal
[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**
Sealable: **No**
Circuit Application: **Signal**
Connector Mounting Type: **Cable Mount (Free-Hanging)**
Shell Plating Material: **Electrodeposited Nickel**

Features

Electrical Characteristics

Operating Voltage	160 VDC
-------------------	---------

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Dimensions

Cable Diameter Range	6 – 10 mm [.23 – .39 in]
----------------------	--------------------------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT

Mechanical Attachment

Mating Retention Type	Speedtec (Triple Start Threaded)
Connector Mounting Type	Cable Mount (Free-Hanging)



Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal
Shielded	Yes

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Shell Type	Metal

Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # ASA012N00410235000
623 PLUG




TE Part # C0-0101-000-P00
CRIMPING TOOL SMALL WITH POSITIONER




TE Part # C0-0235-000-P00
DIGITAL CRIMPING TOOL, SMALL


Customers Also Bought




TE Part #34067
PG BUTT SPLC 22-16COMM22-18MIL




TE Part #794941-1
08P MINI UMNL CAP HSG




TE Part #794940-1
06P MINI UMNL CAP HSG




TE Part #794995-1
MINI UMNL CAVITY PLUG SEAL




TE Part #ASA876N0085200A000
617 PLUG



TE Part #AKA020N00410240000
623 EXTENSION, SPEEDTEC-READY



TE Part #AKA020N00620100000
623 EXTENSION, SPEEDTEC



TE Part #40-B024-000-000
912 insulation insert, 10-pin



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_AKA013N00410240000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_AKA013N00410240000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_AKA013N00410240000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AKA013N00410240000

English

fuer Datenblaetter, die online konfigurierbar sind

German

Product Specifications

German