

Neohm | Neohm CPF

TE Internal #: 1879438-6

Surface Mount Precision Resistor, Thin Film, 0805, .1 W, 51 ohm, .1

%, ± 15 ppm/ $^{\circ}$ C, Solder, 2 Terminations, Height .55 mm [.022 in],

Neohm CPF

[View on TE.com >](#)

Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0805

Power Rating: .1 W

Resistance Value: 51 Ω

Features

Industry Standards

Moisture Sensitivity Level

1

Usage Conditions

Operating Temperature Range

-55 – 155 $^{\circ}$ C

Temperature Coefficient

 ± 15 ppm/ $^{\circ}$ C

Product Type Features

Resistor Type

Precision Resistor

Element Type

Thin Film

Package Size Code

0805

Configuration Features

Number of Resistors

1

Electrical Characteristics

Power Rating

.1 W

Resistance Value

51 Ω

Resistance Class	Up to 1k Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm [.022 in]
Product Length	2 mm [.079 in]
Product Width	1.25 mm [.049 in]

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}$ C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Neohm CPF



Surface Mount Resistors(5842)

Customers Also Bought

TE Part #7-2176416-2
9W STD M/OX 5% 47KTE Part #9-1879621-9
H4P 120K 1% 50PPMTE Part #8-1879642-2
H8 470K 0.1% 100PPMTE Part #1676173-3
RN 0805 12K4 0.1% 10PPM 5KRLTE Part #D67366-000
WP-610419-2.5-9TE Part #1879438-8
CPF0805 51R 0.1% 15PPM 5K RLTE Part #1879438-5
CPF0805 5R36 0.1% 15PPM 1K RLTE Part #4-1618276-4
K62A841=RELAY, VACUUM, SPST

Documents

Product Drawings

CPF0805 51R 0.1% 15PPM 1K RL

English

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English