




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: .3 – 1.3 mm²

Stud Size: M2.5

Stud Diameter: 3.02 mm [.119 in]

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Product Weight	.748 g
Insulation Sleeve Color	Red
Stripe Color	Red

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece



Product Type Features

Terminal Features	Sheared
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M2.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	.3 – 1.3 mm ²
Stud Diameter	3.02 mm [.119 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	17.5 mm [.689 in]
Compatible Insulation Diameter (Max)	3.6 mm [.141 in]
Compatible Insulation Diameter Range	2.7 – 3.6 mm [.106 – .142 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	




Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 47806-2 DIES PIDG 22-16 DIE SET	 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 47386 DAHT PG PIDG 26-16 ASSY	 TE Part # 59170 T-HEAD PIDG SH 26-14 ASSY
 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 539691-2 ERGO DIE R.B.Y	 TE Part # 169404 CERTI-LOK DIE	 TE Part # 2063030-1 SDE DIESET, RBY, UL



TE Part # 59300
T-HEAD PIDG PG 26-16 ASSY

TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY

TE Part # 59250
T-HEAD PIDG 26-14 ASSY

Also in the Series

PLASTI-GRIP

Compression Connectors(3)

Crimp Wire Pins, Tabs & Ferrules(20)

Ring Terminals(310)

Spade Terminals(159)

Splices(45)

Customers Also Bought

TE Part #6609035-9
10ESK1=F7230 S0

TE Part #5223955-2
TE UPM Ver Receptacle 3P STD Power

TE Part #2-2319847-8
END STACK DIP 7P G RAISED T&R

TE Part #5053282035
RNF-100-3/4-9-STK

TE Part #5747872-4
15 PLUG SP/FMS STD

TE Part #2-327950-1
PIDG RECT 22-16COMM 22-18MIL 5


TE Part #1337812-1
50 OHM COAX SMA ELB PLUG ELB P

TE Part #275925-000
CWT-3806-W2



TE Part #1-963215-1

16P STIFTWANNE 3MM



TE Part #7-6437244-1

S14P22F-A

Documents

Product Drawings

22-16 F.E.P.G.RING TONGUE NO.6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_342101-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_342101-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_342101-1_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English