

MPS-MT SN - Test plug

3212251

<https://www.phoenixcontact.com/us/products/3212251>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, with solder connection up to 1 mm² conductor cross section, tin-plated surface, number of positions: 1, color: silver

Your advantages

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm diameter
- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of the terminal blocks from the CLIPLINE complete system or in the test pick-offs provided

Commercial data

Item number	3212251
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z3X
Catalog page	Page 438 (C-1-2019)
GTIN	4046356517393
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.205 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1

Electrical properties

Nominal voltage U_N	60 V DC (30 V AC)
Nominal current I_N	10 A

Connection data

Connection method	Solder connection
-------------------	-------------------

Dimensions

Height	28.5 mm
Length contact range	10.85 mm
Pin diameter	2.3 mm
Note on dimensions	Length without insulating sleeve

Material specifications

Color	silver-colored
Material	Tin-plated brass

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

MPS-MT SN - Test plug

3212251

<https://www.phoenixcontact.com/us/products/3212251>



Classifications

ECLASS

ECLASS-11.0	27440313
ECLASS-12.0	27440313
ECLASS-13.0	27250304

ETIM

ETIM 9.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

MPS-MT SN - Test plug

3212251

<https://www.phoenixcontact.com/us/products/3212251>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com