

1-2308350-5  ACTIVE

## Rail D-Sub Backshells


TE Internal #: 1-2308350-5

Crimp Barrel, Shielded, Rail D-Sub Backshells

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Strain Relief > Crimp Barrel for D-Sub Connectors



Strain Relief Accessory Type: **Crimp Barrel**

Shielded: **Yes**

Thread Size: **None**

Operating Temperature Range: **-40 – 90 °C [ -40 – 194 °F ]**

EU RoHS Compliance: **Compliant with Exemptions**

[All Crimp Barrel for D-Sub Connectors \(22\)](#)

## Features

### Product Type Features

Strain Relief Accessory Type	Crimp Barrel
------------------------------	--------------

### Operation/Application

Shielded	Yes
----------	-----

### Mechanical Attachment

Thread Size	None
-------------	------

### Usage Conditions

Operating Temperature Range	-40 – 90 °C [ -40 – 194 °F ]
-----------------------------	------------------------------

### Other

EU RoHS Compliance	Compliant with Exemptions
--------------------	---------------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024  
(241)Candidate List Declared Against: JAN 2021  
(211)SVHC > Threshold:  
Pb (3.5% in Component Part)

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-2823558-1  
CRIMP INSERTS\_AWG22 / AWG26 (7.0 X 8.0)




TE Part # 2-2308349-0  
CRIMP FLANGE 10 SMALL




TE Part # 1-2308348-5  
CRIMP FLANGE 5 LARGE


## Also in the Series | Rail D-Sub Backshells




Connector Contacts(5)



Connector Hardware(19)







Connector Strain Relief(67)



D-Sub Backshells &amp; Clamps(55)

## Customers Also Bought

TE Part #178086-000  
222A111-25/86-0TE Part #CAT-M5833-F3492A  
Female-on-Board Connector, Top EntryTE Part #1-1437719-2  
T01-0540-P05-MALE PLUG CONNECTOR-CRIMPTE Part #5-1437720-5  
T01-CRIMP-P05=TRIADTE Part #5-1437720-4  
T01-CRIMP-P03TE Part #CONSMB001-G  
SMB Jack 50 Ohm PCB Through HoleTE Part #8-1768048-1  
TKM75-NTE Part #8-1768016-9  
CSL-05525P-9TE Part #5-1768034-7  
LEB-A4PM-X

## Documents

### Product Drawings

#### CRIMP BARREL5

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-2308350-5\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-2308350-5\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-2308350-5\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[Rail D-Sub Backshells Flyer](#)

English