








D




C



- NOTES
- MATERIALS:
PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
SHELL: STAINLESS STEEL
CONTACT: COPPER ALLOY.
PICK AND PLACE TAPE: POLYIMIDE FILM.
 - FINISH:
TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
SOLDER AREA: MATTE TIN PLATING 100u" MIN.
UNDER PLATING: NICKEL PLATING 50u" min OVER ALL.
SHELL: UNDER PLATING: NICKEL PLATING 50u" min OVERALL.
 - HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-72

- 4 TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.
- 5 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.

600	20	200	CHINA	PHILIPPINES		W/CAP	30u" GOLD	2.00MM	3.00MM	5-2381578-7								
				W/O CAP	15u" GOLD	1.20MM	1.20MM	4-2381578-9										
					W/CAP	30u" GOLD	1.20MM	1.20MM	3-2381578-9									
				W/O CAP		15u" GOLD	1.20MM	1.20MM	2-2381578-9									
					W/PICK AND PLACE TAPE	30u" GOLD	1.20MM	1.20MM	1-2381578-9									
				W/O CAP		15u" GOLD	1.20MM	1.20MM	2381578-9									
					W/O CAP	30u" GOLD	2.00MM	3.00MM	2-2381578-7									
				W/CAP		30u" GOLD	2.00MM	4.20MM	1-2381578-8									
					2.00MM		3.00MM	1-2381578-7										
					2.00MM		2.20MM	1-2381578-6										
					2.00MM		1.50MM	1-2381578-5										
					2.00MM		4.20MM	1-2381578-4										
					15u" GOLD	2.00MM	3.00MM	1-2381578-3										
						2.00MM	2.20MM	1-2381578-2										
						2.00MM	1.50MM	1-2381578-1										
						W/PICK AND PLACE TAPE	30u" GOLD	2.00MM	4.20MM	2381578-8								
								2.00MM	3.00MM	2381578-7								
				2.00MM	2.20MM			2381578-6										
				2.00MM	1.50MM			2381578-5										
				2.00MM	4.20MM			2381578-4										
				15u" GOLD	2.00MM	3.00MM	2381578-3											
					2.00MM	2.20MM	2381578-2											
					2.00MM	1.50MM	2381578-1											
					Q'TY/CARTON		POCKET TAPE PITCH		Q'TY/REEL		MADE IN COUNTRY		CAP OPTION		2 CONTACT FINISH		DIM B	

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN: LEO LI 21-OCT-2020		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK: DAVID ZHANG 21-OCT-2020			
mm				APVD: DAVID ZHANG 21-OCT-2020		NAME	
		0 PLC ±0.30		PRODUCT SPEC		MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD. 124P, SMT TYPE, 85ohm	
		1 PLC ±0.20		108-60133			
		2 PLC ±0.10		APPLICATION SPEC			
		3 PLC ±0.10		114-60030			
		4 PLC ±0.10					
MATERIAL		FINISH		WEIGHT		SIZE	
-		-		-		A	
CUSTOMER DRAWING				SCALE 5:1		DRAWING NO	
				SHEET 1 OF 5		C=2381578	
				REV A3		RESTRICTED TO	


D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-







RECOMMENDED PCB LAYOUT
(GENERAL TOLERANCES: ±0.05)

SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 21-OCT-2020		
		CHK: DAVID ZHANG 21-OCT-2020		
DIMENSIONS: mm		APVD: DAVID ZHANG 21-OCT-2020	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 85ohm	
		PRODUCT SPEC: 108-60133		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC: 114-60030	SIZE: A CAGE CODE: 00779 DRAWING NO: 2381578	
		WEIGHT: -		
MATERIAL: -	FINISH: -	CUSTOMER DRAWING	SCALE: 5:1	SHEET: 2 OF 5
			REV: A3	




P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

RECOMMENDED AIC MATING CARD DIMENSIONS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 21-OCT-2020		
		CHK: DAVID ZHANG 21-OCT-2020		
DIMENSIONS:		APVD: DAVID ZHANG 21-OCT-2020	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 85ohm	
mm		PRODUCT SPEC: 108-60133		
		APPLICATION SPEC: 114-60030	SIZE: A CAGE CODE: 00779 DRAWING NO: 2381578	
		WEIGHT: -	RESTRICTED TO: -	
MATERIAL: -		CUSTOMER DRAWING		SCALE: 5:1
				SHEET: 4 OF 5
				REV: A3

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: LEO LI 21-OCT-2020		
		CHK: DAVID ZHANG 21-OCT-2020		
DIMENSIONS:		APVD: DAVID ZHANG 21-OCT-2020	NAME: MINI COOL EDGE 10 INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 85ohm	
mm		PRODUCT SPEC: 108-60133		
		APPLICATION SPEC: 114-60030	SIZE: A 00779 C=2381578	
		FINISH: -	RESTRICTED TO: -	
MATERIAL: -		WEIGHT: -	SCALE: 5:1	
-		CUSTOMER DRAWING	SHEET 5 OF 5	
			REV A3	